

Models 6888-180, 6888-300
XLR Jack / 1/4" Stereo Plug Cable 15, 25 feet

Model 6888-180*, -300* XLR Jack / 1/4" Stereo Plug Cable 15, 25 feet.

*Length of cable only.

Convert XLR to 1/4" stereo with your audio applications

Features

- Audio cable includes 3-pin female XLR connector and 1/4" plug.
- Tarnish resistant silver streamlined profile with compact shell. Rugged construction.
- Flexible and soft low-noise cable.

Materials

- XLR connector bodies are die-cast zinc alloy with tarnish resistant nickel finish.
- 1/4" stereo plugs are nickel-plated machined brass.
- Contacts are nickel-plated brass.
- Strain relief clamp designed for durability: POM (Polyoxymethylene).
- Cable made from soft PVC low-noise microphone cable.

Specifications

Cable Type	Soft PVC low noise microphone cable.
Cable Lengths	6869-180: 180 in (15 ft or 4.572 meters) 6869-300: 300 in (25 ft or 7.62 meters)
Cable O.D.	6.0 mm (0.24 in)

Ordering Information

Model: 6888-180, -300

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.