



NSB2B-16/0

Type B, length 2, 16 IN (female/send)

Width: 117 mm, height: 79 mm, length: 252 mm

Supplied as disassembled set comprising of all hardware parts including plates, profiles, strain relief, end pieces and screws.



Technical Information

[hide](#)

Product

Title	NSB2B-16/0
-------	------------

Electrical

Contact resistance	< 5 mΩ (inner)
--------------------	----------------

Dielectric strength	0.5 kVdc
---------------------	----------

Insulation resistance	≥ 1 GΩ
-----------------------	--------

Rated current per contact	2 A
---------------------------	-----

Mechanical

Cable O.D.	15 - 20 mm multicore
------------	----------------------

Insertion force	≤ 10 N
-----------------	--------

Withdrawal force	≥ 10 N
------------------	--------

Lifetime	> 1000 mating cycles
----------	----------------------

Wiresize	0.22 and 0.14 mm²
----------	-------------------

Wiresize	24 and 26 AWG
----------	---------------

Material

Shell	Aluminium
-------	-----------

Quad plates	POM
-------------	-----

End pieces	Thermoplastic
------------	---------------

Environmental

Temperature range	-25 °C to +70 °C
-------------------	------------------

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

