



4

3


2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		H2	REVISED PER ECO-07-008008	10APR07	JDP	CWR



- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 2.54μm [.000100] MIN TIN-LEAD OVER 1.27μm [.000050] MIN NICKEL.
- 3 TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 4 ACCEPTS #2 SELF-TAPPING SCREW, .250 LONG REF.
- 5. MATES WITH 6 POSITION SHIELDED DIN PLUG 212437-4.
- 6 BRASS PER ASTM B36.
- 7 2.54μm [.000100] MIN TIN OVER 1.27μm [.000050] MIN NICKEL.



OBSOLETE	7	9-211509-0
	2	211509-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	8/12/91	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK	A.STAUB BG				
		APVD	-	NAME			
		PRODUCT SPEC	108-10047	RECEPTACLE ASSY, RIGHT ANGLE, 6 POSITION, CIRCULAR DIN			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	114-40025				
MATERIAL		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
1		CUSTOMER DRAWING	-	A2	00779	C=211509	-
SEE TABLE		SCALE	4:1	SHEET	1 OF 1	REV	H2