

Thermomagnetic device circuit breaker - TMC 61C 03A - 0902043

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Thermomagnetic circuit breaker, one-pole, 3.0 A thermal trip. DIN rail mounted and UL 1077-recognized with optional auxiliary contact for either S or H remote signal. Protects wiring and equipment from overcurrent and short circuit faults.

Key commercial data

Packing unit	1
Minimum order quantity	72
GTIN	 4 046356 557962
Custom tariff number	85362010
Country of origin	HUNGARY

Technical data

Product type	Thermomagnetic device circuit breakers
Approval	CSA
Approval	UL Recognized
Approval	cUL Recognized
Approval	cULus Recognized
Mounting type	DIN rail: 35 mm
Nominal current IN	3 A

Classifications

eclass

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116

etim

ETIM 3.0	EC000899
ETIM 4.0	EC000899

unspsc

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411

Thermomagnetic device circuit breaker - TMC 61C 03A - 0902043

Classifications

unspsc

UNSPSC 13.2	39121411
-------------	----------

Approvals

Certificates

Certification

CSA / UL Recognized / cUL Recognized / cULus Recognized

Certification EX

Certification submitted

Approval details

CSA

UL Recognized

cUL Recognized

cULus Recognized

Accessories

Accessories

Bridges

Wiring bridge - MPB 18/1- 3 - 2809212



Wiring bridge for modules with connecting pitch 17.5 mm, 1-phase, 3-pos.

Thermomagnetic device circuit breaker - TMC 6LOCKOUT - 0902467

Locking element for TMC 6 circuit breakers

