

# **RAFIX 22 QR - Lamp socket, screw terminals, with diode and series resistor 130 V, without coupling**

**5.00.070.080/0000**


## **Dimensions**

Dimensions with coupling	39.5 x 49.9 x 30 mm
Mounting depth without cable	56.4 mm

## **Mechanical design**

Mounting	snap on coupling and actuator
Diode and resistor	yes
Terminals	screw terminals
Terminal marking	X1 = anode, X2 = cathode

## **Lamp characteristics**

Lamp socket	BA 9 s
Operating voltage AC/DC	250 V
Lamp power max.	2 W
Lamp voltage	130 V

## **Other specifications**

Approvals	ENEC 10/15; ULc
Robustness	acc. to IEC 60947-5-5
Shock resistance acc. to IEC 60068-2-27	50 g at 11 ms, amplitude half sinusoidal
Resistance to vibrations acc. to IEC 60068-2-6	10 g at 40 ... 500 Hz
Environmental resistance	acc. to IEC 60068-2-14, -30, -33 and -78
Ambient temp. operating max.	+70 °C
Storage temperature min.	-40 °C
Ambient temp. operating min.	-25 °C
Storage temperature max.	+80 °C
Flame class acc. to UL 94	V 0
Hot wire ignition acc. to IEC 60695-2-1	yes
ROHS compliant	yes
REACH compliant	yes

with contact block

