


NYLON HEXAGONAL PILLARS & SPACERS


- Nylon 66 moulding, brass insert, mild steel stud (zinc plated)
- Custom lengths available. Please contact Technical Sales for a quotation.



MALE/FEMALE



FEMALE/FEMALE



Material	Nylon Moulding, Brass Insert, Steel Stud			Nylon Moulding, Brass Insert		
Style	Male/Female			Female/Female		
Thread	M3	M4	M6	M3	M4	M6
Across Flat	7.0mm	8.0mm	16.0mm	7.0mm	8.0mm	16.0mm
L2 (Stud)	6.0mm	6.0mm	12.7mm			
L3	6.0mm	6.0mm	12.7mm	6.0mm (*5.5mm)	6.0mm	12.7mm (*12.0mm)
Length mm						
12	R30-7351200			*R30-5351200		
14	R30-7351400			R30-5351400		
15		R40-7351500			R40-5351500	
16	R30-7351600			R30-5351600		
18	R30-7351800			R30-5351800		
20	R30-7352000	R40-7352000		R30-5352000	R40-5352000	
22	R30-7352200			R30-5352200		
24	R30-7352400			R30-5352400		
25		R40-7352500	R60-7352500		R40-5352500	*R60-5352500
26	R30-7352600			R30-5352600		
28	R30-7352800			R30-5352800		
30	R30-7353000	R40-7353000	R60-7353000	R30-5353000	R40-5353000	R60-5353000
35	R30-7353500	R40-7353500	R60-7353500	R30-5353500	R40-5353500	R60-5353500
40	R30-7354000	R40-7354000	R60-7354000	R30-5354000	R40-5354000	R60-5354000
45		R40-7354500	R60-7354500		R40-5354500	R60-5354500
50		R40-7355000	R60-7355000		R40-5355000	R60-5355000
55		R40-7355500	R60-7355500		R40-5355500	R60-5355500
60		R40-7356000	R60-7356000		R40-5356000	R60-5356000
65			R60-7356500			R60-5356500
70			R60-7357000			R60-5357000