

| REV. | DESCRIPTION | DATE       |
|------|-------------|------------|
| A    | RELEASE     | 2012.11.12 |

RoHS

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: TiN, 80-100μ”

Contact Material: Brass




Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.


Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



| NUMBER<br>OF POSITIONS | DIMENSIONS |       |       |
|------------------------|------------|-------|-------|
|                        | A          | B     | C     |
| 06                     | 26.92      | 5.08  | 22.86 |
| 08                     | 29.46      | 7.62  | 25.40 |
| 10                     | 32.00      | 10.16 | 27.94 |
| 12                     | 34.54      | 12.70 | 30.48 |
| 14                     | 37.08      | 15.24 | 33.02 |
| 16                     | 39.62      | 17.78 | 35.56 |
| 20                     | 44.70      | 22.86 | 40.64 |
| 24                     | 49.78      | 27.94 | 45.72 |
| 26                     | 52.32      | 30.48 | 48.26 |
| 30                     | 57.40      | 35.56 | 53.34 |
| 34                     | 62.48      | 40.64 | 58.42 |
| 40                     | 70.10      | 48.26 | 66.04 |
| 50                     | 82.80      | 60.96 | 78.74 |
| 60                     | 95.50      | 73.66 | 91.44 |
| 64                     | 100.58     | 78.74 | 96.52 |



| UNLESS TOLERANCE                                                                   |                                                                                    | DRAW BY    |       | Cnc Tech,LLC      |
|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------|-------|-------------------|
| GENERAL                                                                            | ANGLE                                                                              | DESIGN BY  |       |                   |
| X. ± 0.30                                                                          | X.° ± 3.0°                                                                         | CHECK BY   |       |                   |
| .X ± 0.20                                                                          | .X° ± 2.0°                                                                         |            |       |                   |
| .XX ± 0.15                                                                         | .XX° ± 1.0°                                                                        |            |       |                   |
| .XXX ± 0.08                                                                        | .XXX ± 0.5°                                                                        | APPROVE BY |       |                   |
|  |  | SCALE      | SHEET | UNIT              |
|                                                                                    |                                                                                    | 1:1        | 1/1   | MM                |
| Part NO.                                                                           |                                                                                    |            |       | 3010-XX-003-12-99 |
| DRAW NO:                                                                           |                                                                                    |            |       |                   |
| REV: A                                                                             |                                                                                    |            |       |                   |