


BES M08MI-NSC15B-BV03

Inductive Sensors

NPN
NO
flush mountable

BALLUFF
sensors worldwide



PX1571

Electrical data:

Connection	cable
Rated operational voltage (Ue)	24 DC V
Load current capacity (Ie)	100 mA
Electrical type	DC
Utilization category	DC 13
No-load supply current damped	= 12 mA
No-load supply current undamped	= 12 mA
Off-state current max (Ir)	20 µA
Switching output	NPN
Switching element function	NO
Operating frequency (f)	600 Hz
Voltage drop max. static	3 V
Supply voltage max. (Ub)	30 V
Supply voltage min. (Ub)	12 V


Mechanical data:

Number of wires	3-wire
Rated operating distance (sn)	1,5 mm
Diameter	M 8 mm
Assured operating distance	0...1,2 mm
Cable code designation	LiYY-O
Mounting	flush mountable
Ambient temperature max	+70 °C
Ambient temperature min	-25 °C
Sensing face material	PBT
Housing material	CuZn, nickel plated
Repeat accuracy max. (R)	= 5 %

General data:

Output indication	yes
Short circuit protected	yes
Brand	GlobalProx
Degree of protection IP	IP67
Protected against polarity reversal	yes
Approval	CE

wiring



www.balluff.com

Balluff Europe: +49 7158 173 -0
Balluff USA: 1-800-54 3-83 90
Balluff Asia: +86 21-50 64 41 31

Online Productinformation
2008-02-15