



FEATURES:

- Breakout converts BNC (Female) cables/connectors to Micrograbber® Test Clips for test versatility.
- BNC connector and grabber cap are molded directly to the wire for pull strength durability and dust/moisture resistance.
- Grabber hook and BNC center contact are beryllium copper for superior strength.
- Grabber hook and BNC center contact are gold plated for optimum corrosion resistance and low contact resistance.

MATERIALS:

BNC: Body – Brass, Nickel Plated, Center Contact – Brass, Gold Plated.

Wire: 20 AWG, Stranding 41 x 36 T.C., PVC Insulated, .087" (2,21 mm) O.D.

Marking: Model 5189, Color matches Grabber.

Grabber: Contact – Beryllium Copper, Gold Plated

Spring – Stainless Steel

Insulation – Glass Filled Nylon. Color: one red, one black

RATING:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 150 VRMS

Operating Temperature: +55°C (+131°F) Max.

ORDERING INFORMATION:

Model 5189
Custom lengths are available, contact Pomona Technical support: 800-241-2060
(Technicalsupport@pomonatest.com)

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com