

(1.27 mm) .050"

ISDF, CC03R, CC03M, TFM SERIES

DISCRETE WIRE COMPONENTS & TOOLING

SPECIFICATIONS

For complete specifications see www.samtec.com?ISDF, www.samtec.com?CC03R or www.samtec.com?CC03M

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality





FILE NO. E111594

TOOLING

- Hand tool:
CAT-HT-203-2830-12
- Clamp for mounting
hand tool to work table:
CAT-HT-MNT-01
- Mini Applicator:
CAT-MA-203-2830-XX-01

Note: Some lengths, styles and options are non-standard, non-returnable.



Mates with:
SFSD(T), SFSS(T)

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?TFM

Insulator Material: Black Liquid Crystal Polymer
Terminal Material: Phosphor Bronze
Plating: Au or Sn over 50μ" (1.27 μm) Ni
Voltage Rating: 250 VAC mated with SFM
Operating Temp Range: -55°C to +125°C
RoHS Compliant: Yes

Processing:
Lead-Free Solderable: Yes
SMT Lead Coplanarity: (0.10 mm) .004" max (05-25) (0.15 mm) .006" max (30-50)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594



FILE NO. 090071_0_000

