

PSR 12



Bosch Cordless Drill/Driver PSR 12

Compact and powerful

- Powerful 12 V motor with planetary gears
- Torque preselection with 10 torque settings plus a drill setting – optimum power for every application
- Twin-sleeve "Click" keyless chuck – easy, tool-free bit changes



Keyless chuck



Forward/reverse indicator



Quick-change battery pack

- Bosch Electronic speed control: "accelerate" from 0 – max. using the trigger switch
- PowerLight – thanks to the built-in LED, your workpiece is always well lit and clearly visible
- Run-out brake and switch-on lock
- Quick-change battery pack
- Softgrip for a better and more comfortable hold
- Bit storage compartment on the housing

Part no. 0 603 955 570

- 1 battery
- Charger
- Carrying case

Part no. 0 603 955 571

- 2 batteries
- Charger
- Carrying case

Technical data

No-load speed	0 – 700 rpm
Max. torque for soft/hard screwdriving applications	11 / 26 Nm
Torque settings	10 + 1
Battery voltage	12,0 V
Chucks	Keyless chuck
Machine weight with battery	1,40 kg
Screw diameter	
Screw diameter up to	8 mm
Drilling diameter	
Drill diameter in steel	10 mm
Drill diameter in wood	20 mm

Functions

- Bosch Electronic
- Drilling screws
- Forward/reverse operation
- Softgrip
- Integrated work light (PowerLight)