


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #		STUD SIZE	DIMENSIONS mm				
			A $\pm 0,51$	W $\pm 0,25$	C $\pm 0,38$	M $\pm 0,51$	H $\pm 0,25$
PREFIX	PK						
PM6-4F	-L -D	M4	19,36 (.76)	7,95 (.31)	7,11 (.28)	13,97 (.55)	4,32 (.17)
PM6-5F	-L -D	M5	19,36 (.76)	9,52 (.37)	7,11 (.28)	13,97 (.55)	5,33 (.21)
PM6-6F	-L -D	M6	22,61 (.89)	10,92 (.43)	8,64 (.34)	16,26 (.64)	6,60 (.26)

NOTES:

1. USED FOR:
A. 2,5-6,0mm² (#12-10 AWG), SOLID
OR STRANDED, COPPER WIRE
2. MATERIAL:
A. STAMPING - 1,02mm (.04) THK COPPER, TIN PLATED
3. DIMENSIONS IN BRACKETS ARE IN INCHES
4. PACKAGE QTY:
A. STD: L=50
B. BULK: D=500
5. WIRE STRIP LENGTH: 7,1 ⁺⁸₋₀ (9/32 ^{+1/32}₋₀)
6. INSTALLATION TOOLS: REF. DWGS.
A41522, A41523, A41524, A41525



A41429_02

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
02	10/97	TM		CHANGED DECIMAL POINTS TO COMMAS				NON-INSULATED METRIC FORKS 2,5-6,0mm ² BARREL			
01	1/97	TM	RLS	UPDATED DIMENSIONS FILESPEC WAS NPC_A41429_00	05478	LA	DH				
00	7-90	BK	RLS	RELEASED	00687	LA	KRS				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								BDK		NONE	A41429