






REV.	DATE	DESCRIPTION
A	08/15/04	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE
HEX. CRIMP SIZE .178"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .042"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	G.R.S.	08/15/04								
7						CHECKED										
6										PART DESCRIPTION						
5	FERRULE	BRASS	NICKEL	1						BNC CRIMP PLUG – 75ohms (FOR RG179, BELDEN 9221/1502A/1522A)						
4	SLEEVE	DELRI	NATURAL	1						PART NO.						
3	CONTACT PIN	BRASS	GOLD	1						112954						
2	INSULATOR	TEFLON	NATURAL	1						DWG. NO.						
1	BODY	BRASS	NICKEL	1						112954.DWG						
	DESCRIPTION	MATERIAL	FINISH	QTY				DWG. FILE		C:/112/112954.DWG		REV.	A	SIZE	A	SCALE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112954](#)