




- MAT'L:
- 1.CABLE:UL2919,3COAXIAL+7C+1+AL/MY+BRAID,0.D:8.5
 - 2.CONNECTORS:HD15M,9th EMPTY,BLACK
 - 3.THUMBSCREW:#4-40UNC,E32
 - 4.BLACK HEAT SHRINK:ø1.5 X 15:6PCS
 - 5.COPPER SIZE:30 X 50
- NOTE:
- 1.TOTAL LENGTH:10000±50mm
 - 2.COLOR:BEIGE
 - 3.MOLDED TYPE
 - 4.360° SOLDER
 - 5.ROHS COMPLIANT

CONFIGURATION:

1	RED(COAX.)	1	HD15F
6	RED(GROUND)	6	
2	GREEN(COAX.)	2	
7	GREEN(GROUND)	7	
3	BLUE(COAX.)	3	
8	BLUE(GROUND)	8	
4	BROWN	4	
5	BLACK	5	
13	GREEN	13	
14	RED	14	
10	ORANGE	10	
11	WHITE	11	
12	YELLOW	12	
	(BRAID)		SHIELD

RoHS
Compliant

DATE	15 JAN,1999	PARTS NO	MN3073N	TITLE:	HD15 MALE-HD15 FEMALE	AK3750X 10M ASSMANN ELECTRONICS,INC.		
UNIT	MM	DRAWN NO	000240		(MOLDED TYPE)			
SCALE		BUYER NO	002					

NO.	DESCRIPTION	QTY
④	THUMBSCREW:#4-40UNC,E32	4
③	#28,UL2919,3COAX+7C+1+AL/MY+B,0.D:8.5 10M	
②	HD15F,BLACK	1
①	HD15M,9th EMPTY,BLACK	1