

FED. MFG. CODE 91929

(LEFT HAND)

DDM/CAD

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK	
-------	--


MAM	1600
-----	------



HEX SEAL NUT (.938) ACROSS FLATS-


ELASTOMER PLUNGER SEAL
SECURED TO COMPONENTS
BY EXTERNAL BANDING

HARDENED STEEL PLUNGER-



1/2-14 NPT THREAD-

3X Ø.265




NOTE

1 - 8-32 UNC X (.219) BINDER HEAD COMBINATION, TERMINAL SCREWS AND CUPWASHERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

ELECTRICAL DATA

SCALE	FULL
-------	------

DO NOT SCALE PRINT

OPERATING FORCE — — — 2 1/2 LBS MAX

CONTACT ARRANGEMENT
S P D T

DIFFERENTIAL TRAVEL — — — .010 MAX

L23

20A 125, 250 OR 480 VAC
10A 125 VAC "L"

OVERTRAVEL — — — — — .219 MIN

1HP 125 VAC, 2HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC



WEIGHT	.500 LB
--------	---------

ANSI Y14.5M-1982 APPLIES