


Number of contacts

6-64



Male header with straight solder pins

Identification	No. of contacts	Part No.					
		Without levers		With short levers		With long levers	
Male header with straight solder pins Length: 2.9 mm	6	09 18 506	└ 924	09 18 506	└ 914	09 18 506	└ 904
	10	09 18 510	└ 924	09 18 510	└ 914	09 18 510	└ 904
	14	09 18 514	└ 924	09 18 514	└ 914	09 18 514	└ 904
	16	09 18 516	└ 924	09 18 516	└ 914	09 18 516	└ 904
	20	09 18 520	└ 924	09 18 520	└ 914	09 18 520	└ 904
	24	09 18 524	└ 924	09 18 524	└ 914	09 18 524	└ 904
	26	09 18 526	└ 924	09 18 526	└ 914	09 18 526	└ 904
	30	09 18 530	└ 924	09 18 530	└ 914	09 18 530	└ 904
	34	09 18 534	└ 924	09 18 534	└ 914	09 18 534	└ 904
	40	09 18 540	└ 924	09 18 540	└ 914	09 18 540	└ 904
	50	09 18 550	└ 924	09 18 550	└ 914	09 18 550	└ 904
	60	09 18 560	└ 924	09 18 560	└ 914	09 18 560	└ 904
	64	09 18 564	└ 924	09 18 564	└ 914	09 18 564	└ 904
Male header with straight solder pins Length: 4.5 mm	6	09 18 506	└ 922*	09 18 506	└ 912*	09 18 506	└ 902*
	10	09 18 510	└ 922*	09 18 510	└ 912*	09 18 510	└ 902*
	14	09 18 514	└ 922*	09 18 514	└ 912*	09 18 514	└ 902*
	16	09 18 516	└ 922*	09 18 516	└ 912*	09 18 516	└ 902*
	20	09 18 520	└ 922*	09 18 520	└ 912*	09 18 520	└ 902*
	24	09 18 524	└ 922*	09 18 524	└ 912*	09 18 524	└ 902*
	26	09 18 526	└ 922*	09 18 526	└ 912*	09 18 526	└ 902*
	30	09 18 530	└ 922*	09 18 530	└ 912*	09 18 530	└ 902*
	34	09 18 534	└ 922*	09 18 534	└ 912*	09 18 534	└ 902*
	40	09 18 540	└ 922*	09 18 540	└ 912*	09 18 540	└ 902*
	50	09 18 550	└ 922*	09 18 550	└ 912*	09 18 550	└ 902*
	60	09 18 560	└ 922*	09 18 560	└ 912*	09 18 560	└ 902*
	64	09 18 564	└ 922*	09 18 564	└ 912*	09 18 564	└ 902*
Kinked version on request							

* Not normally kept in stock
For accessories see page 08.18
For dimensions see page 08.11

For performance level 3 please specify digit
For performance level 2 please specify digit
S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

