


4, 5, 8 and 12-Pin Field Wireable Connectors, Standard and Reverse Key

- IEC IP67 Protection



Housing Style	Female Part Number	Male Part Number	Features	Pinout
B 81.. 		BS 8157-0/PG 9	PBT, Black, PG 9 cable gland accepts 6-8 mm cable diameter, spring clamp accepts up to 20 AWG conductors, 85°C, 125 V, 4 A, Mates with standard key 5-pin cordsets and receptacles, spring clamp	Male
	BWS 8141-0	BSWS 8141-0 BSWS 8241-0	PBT, Black, PG 9 cable gland accepts 6-8 mm cable diameter, screw terminals accepts up to 18 AWG conductors, 85°C, 250 V, 4 A, mates with <u>reverse</u> key 4-pin cordsets and receptacles	Female Male
B 82.. 				
	BWS 8151-0 BWS 8251-0	BSWS 8151-0 BSWS 8251-0	PBT, Black, PG 9 cable gland accepts 6-8 mm cable diameter, screw terminals accepts up to 18 AWG conductors, 85°C, 60 V, 4 A, mates with <u>reverse</u> key 5-pin cordsets and receptacles	Female Male
BS 81.. 				
	B 8181-0 B 8281-0	BS 8181-0 BS 8281-0	Nylon, Black, PG 9 cable gland accepts 6-8 mm cable diameter, screw terminals accepts up to 18 AWG conductors, 85°C, 30 VAC/75 VDC, 2 A, mates with standard key 8-pin cordsets and receptacles	Female Male
BS 82.. 				
	B 81121-0/PG 9	BS 81121-0/PG 9	Nylon, Black, PG 9 cable gland accepts 4-8 mm cable diameter, screw terminals accepts up to 24 AWG conductors, 85°C, 30 V, 1 A, mates with standard key 12-pin cordsets and receptacles	Female Male