




FEATURES:

- Breakout converts BNC (Male) cables/connectors to Micrograbber® test clips for test versatility
- BNC connector and Micrograbber test clip cap are molded directly to the wire for pull strength durability and dust/moisture resistance
- Micrograbber test clip hook is Beryllium Copper for superior strength
- Micrograbber test clip hook and BNC center contact are gold plated for optimum corrosion resistance and low contact resistance

MATERIALS:

BNC: Nickel plated Brass

Center Contact: Gold plated Beryllium Copper

Wire: 20 AWG, PVC

Marking: Model 5188

Micrograbber test clip:

Contact: Gold plated Beryllium Copper

Spring: stainless steel

Insulation: Glass filled nylon, color: one red, one black

RATINGS:

Operating Temperature: +55°C (+131°F) Max.

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 150 VRMS

ORDERING INFORMATION: Model 5188

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90457 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com