

Protective caps

Material and finishes

Protective cap	Aluminum alloy
Sash chain	Stainless steel
Cord	Polyamide
Ring	Stainless steel
Clip	Aluminum alloy
Gasket	Fluor Silicone
Endlink / rivet	Stainless steel, passivated
Bayonet pin	Stainless steel, passivated
Finishes	
A34	Nickel
A66	Olive drab chromate over cadmium

How to order

KPT80 - 10 D - A34

MS3180 - 10

Series

KPT80 – for plug

KPT81 – for receptacle

Shell size

8 – 24

Termination

D – Preferred type: with nylon cord and end link clip and end link attached

C – sash chain

N – sash chain with ring (81 or 3181 only)

Modification

A34 – nickel plated

without code = A66 – olive drab chromate over cadmium

VG95328 - Z2 C 10

VG Specification

Style

Z1 – for receptacle

Z2 – for plug

Termination

C – with nylon cord and end link clip and end link attached

Shell size

8 – 24

Crimp tool for clips upon request

80 / 3180 – for plugs
cap with sash chain C or N

80 / 3180 – for plugs
cap with nylon cord D / preferred type

81 / 3181 – for receptacles
cap with nylon cord D / preferred type

Shell	A size	L1 max	B max.	L2 max.	H max.	N
8	18,26	19,84	18,0	21,44	76	14,7
10	21,44	19,84	20,3	21,44	76	17,9
12	25,40	19,84	25,1	21,44	89	22,6
14	28,58	19,84	28,2	21,44	89	25,8
16	31,75	19,84	31,5	21,44	89	29,0
18	34,92	19,84	34,5	21,44	89	32,2
20	38,10	21,44	37,8	21,44	101	35,3
22	41,28	21,44	40,9	21,44	101	38,5
24	44,45	22,22	44,2	22,22	101	41,7

81 / 3181 – for receptacles
cap with sash chain C or N

26

ITT Cannon

Subject to changes