





PRODUCT NO.	CONTACTS	DIM. "A"
88940-001	20	19.96
88940-002	12	11.96
88940-001LF	20	19.96
88940-002LF	12	11.96



ISOMETRIC VIEW

CODE MARKING (OPTIONAL)

CODE MARKING



NOTES:

1. MATERIAL: LCP, 30% GF, COLOR NATURAL
FLAME RETARDANT ACC. UL 94-V0.
2. RECOMMENDED WIRE GAGE:
24-26 OR 28-30 AWG SOLID WIRE.
ALL WIRES APPROVED FOR USE WITH 88940 CONNECTORS
ARE LISTED IN GS-20-002.
3. THE PRODUCTS WHERE THE PART NUMBERS END IN LF
MEET THE EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
4. THESE PRODUCTS LISTED ON THIS DRAWING WILL NOT
WITHSTAND WAVE SOLDER OR REFLOW OPERATIONS.
5. FOR LEADFREE PART NUMBERS, ADD AN 'LF' SUFFIX.
EXAMPLE: 88940-001LF

mat'l. code				surface	tolerance	projection	product family
				ASME Y14.5	ASME Y14.5		METRAL ACC
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
B	V11796	RPM	7/10/01	angles	.X±.3	MM	LOW PROFILE IDC CONNECTOR
C	V20611	CGD	4/15/02	linear	.XX±.13		
D	V06-0118	JRV	3/17/06	0° ±2°	.XXX±.051	scaleNONE	
E	V06-0609	DCH	2006-06-22	dr	J.W. FALKE	2-19-96	dwg no
				enrg	J.R.VOLSTORF	2-19-96	sheet 1 of 1
				chr			size
				appd	J.R.VOLSTORF	2-19-96	88940
							A4
sheet	revision	E					type
index	sheet	1					CUSTOMER Drawing