

- Real 40W replacement lamp
- IP65 rated making it suitable for outdoor applications
- Dimmable
- Long lifetime of 40,000 hours
- Ideal for general lighting in indoor and outdoor applications



IP65

Order Code 52220

General Data

Lamp Socket	E27
Design	Globe

Geometric Data

Length (mm)	122
Diameter (mm)	60
Weight (g)	130

Electric Data


Wattage (W)	7.5
Voltage (V)	220-240
Power Factor	≥ 0.75
Operating Frequency (Hz)	50-60

Photometric Data

Luminous Flux (lm)	480
CRI	≥ 80
CCT (K)	2700
Luminous Intensity (cd)	-
Beam Angle (°)	220
Lifetime (hrs)	40,000

Switching cycle	50,000
-----------------	--------

Wattage Equivalent (W)	40
------------------------	----





Order Code 52220

Product Description LED CLASSIC A E27 7.5W 2700K WW 480LM 220deg DIM

Technical Packaging Details

Barcode	023942522201
EAN 128	(02)00023942522201(37)06(91)09
EAN 14	50023942522206
Pack Dimensions (HxWxL)	138 mm x 74 mm x 72 mm
Pack Weight	188 g
Carton Qty (Shipping Unit)	6
Carton Dimensions (HxWxL)	159 mm x 247 mm x 167 mm
Cartons/Layer	96
Layers/Pallet	6
Units/Pallet	576

Photometric Diagram

52220

