

A-57・A-55 丸型ハンドル

防水平面ハンドル

WATERPROOF ROUND-SHAPED FLUSH HANDLES





A-57-1



キーNo.TAK60
Key


キーNo.0200
Key

パネル穴明け寸法
Panel drilling dimensions





No.TAK60

No.0200



回転角度90°
Turning angle



A-57
亜鉛合金製

特徴 Feature

- 錠前は操作性に優れた防塵シャッター付新型リバーシブルキーTAK60を標準装備(A-57-1-TAK60)
- 左右兼用型
- The lock comes standard with the TAK60, a new-style reversible key with an easy-to-use dustproof shutter. (A-57-1-TAK60)
- For both left-hand and right-hand use.

- 仕様 ●材質: 亜鉛合金 (ZDC)
- 表面仕上: シルバーメタリック塗装
- 付属品: キー2本
- 用途 ●配分電盤・制御盤
- 納期 ●標準在庫品
- 備考 ●特注で表面の赤いラインを左に入れることもできます。
- 鍵違いも製作します。お問合せください。
- 本製品の止め金取付け用ねじは、緩み防止のため「緩み防止剤」の塗布をお奨め致します。
- 止め金は646~650ページの□8穴の中から選びください。

- Specifications ●Material: Zinc alloy (ZDC)
- Finish: Coated silver metallic
- Accessories: Two keys
- Specific use ●Power/distribution and control boards
- Remarks ●It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.
- Select the stopper plate with □8-hole on page 646 to 650.

商品番号 Product No.	RoHS	CAD	コード Code	単価 Price	数量 Quantity	量販価格 Bulk Price
A-57-1-TAK60	●	2D	04077	¥1,900	10個~	¥1,824
A-57-1	●	2D	03304	¥1,900	10個~	¥1,824

●: RoHS指令対応品 ※大量のご注文は更にお安くなります。

▲: RoHS指令に対応可能です。