

48" Metal Power Strip with 12 Outlets, Surge Protected

Specifications

Power Strip Measurement:	L48" x W1.653" x H1.496" (1219 x 42 x 38mm)*
Outlets:	12
Outlet Color:	White
Outlet Orientation:	Horizontal
Plug / Receptacle Type:	NEMA 5-15P / 5-15R
Outlet Spacing:	3-3/4" (95mm) (center to center)
Power Cord:	9' (2.74m) 14/3 AWG, SJT Heavy Duty
Voltage Input/Output:	110-125V 60Hz
Current Input:	15A
Full Load:	1875VA
On/Off Switch:	Yes (lighted)
Circuit Breaker:	Resettable (built in the switch)
Surge Protection:	Up to 1824 Joules
Lines Protected:	(L-N) (L-G) (N-G)
Response time:	Less than 5 nanosecond
Noise Filter:	EMI/RFI
Mounting on Back:	Yes
Mounting Tabs:	N/A
Mounting Clips:	3/4" (19mm) Spring Steel Clips included
Indicator:	Green LED for Grounding and Surge Protection

Notes

* Measurement is approximate. For installation purposes: The length of the power strip does not include the mounting tabs (approx. 0.624"/15.8mm on both ends), if any; the width does not include the size of screws (min. 0.064"/1.6mm on each side); the height does not include the receptacles (about 0.208"/5.3mm above the surface of the strip).

For use in countries and regions with 110-125V 60Hz only. Not intended for use in or around wet or potentially wet areas.