


Fan Vibration Absorber

For Fans from 40mm to 119mm




Features:

- Easy to attach axial fans with patented fastening elements.
- No tools or screws are required.
- Fan vibration absorbers greatly reduce the transmission of vibrations to the panel.
- Housing causing a reduction in the level of noise up to 9 decibels.
- Fan vibrations are absorbed by the flexible sleeves, thereby reducing damage and increasing the life span of the fan.
- Product accessories include screwless, mountable plastic finger guards, filter media, EMI shields, filter guards and rivets.
- The fan vibration sleeves and accessories will fit most fan manufacturer's products.

Fan Vibration Sleeves

Material : TPE (thermoplastic elastomer) RoHS compliant.
Color : Black.
Hardness : ca 70° Shore A.



Fan Vibration Absorber

For Fans from 40mm to 119mm




Specifications

Description	A	B	C	D	E	F	G	H	S	Panel Thickness	Part Number
Fan Sleeve, 40mm	1.692 (43)	11.574 (40)	1.496 (38)	0.177 (4.5)	0.581 (14.75)	0.207 (5.25)	0.008 (2.0)	0.138 (3.5)	0.039 (1.0)	0.0030 (0.75) to 0.049 (1.25)	MC-QLM-40-20-10
Fan Sleeve, 60mm	2.520 (64)	2.362 (60)	2.283 (58)	0.197 (5.0)	0.689 (17.5)	0.295 (7.5)	0.012 (2.0)	0.157 (4.0)			MC-QLM-60-30-10
Fan Sleeve, 80mm	3.307 (84)	3.150 (80)	3.031 (77)	0.228 (5.8)	0.728 (18.5)	0.335 (8.5)	0.016 (4.0)				MC-QLM-80-40-10
Fan Sleeve, 92mm	3.819 (97)	3.622 (92)	3.504 (89)	0.236 (6.0)	0.768 (19.5)	0.374 (9.5)					MC-QLM-92-40-10
Fan Sleeve, 119mm	4.921 (125)	4.685 (119)	4.567 (116)	0.315 (8.0)	0.945 (24.0)	0.413 (10.5)	0.020 (5.0)	0.177 (4.5)			MC-QLM-119-50-10

Dimensions: Inches (Millimetres)

Part Number Explanation



Panel Thickness : 10 = Panel thickness from 0.75 to 1.25mm.


Fan Vibration Absorber

For Fans from 40mm to 119mm



Plastic Fan Guards

Material : Plastic.
 Color : Black.
 Equal Guideline : 2002/95/EG (RoHS compliant).




Specifications

Description	A	B	C	D	E	F	G	Part Number
Finger Guard, 92mm	3.976 (101.0)	3.248 (82.5)	3.622 (92.0)	1.181 (30.0)	0.594 (15.1)	0.335 (8.5)	0.098 (2.5)	MC-QSG-92-02
Finger Guard, 119mm	5.039 (128.0)	4.133 (105.0)	4.685 (119.0)	1.654 (42.0)	0.654 (16.6)	0.354 (9.0)	0.118 (3.0)	MC-QSG-119-02

Dimensions: Inches (Millimetres)

Part Number Explanation



Type : 02 = See dimension "A". Panel hole layout hidden
 Only available in 92mm and 119mm sizes.




Fan Vibration Absorber

For Fans from 40mm to 119mm



EMI Filter Shields

Material : High-grade steel (spring V2a)/material No. 1.4310.
 Material Thickness: : 0.2mm to 0.3mm.




Specifications

Description	A	B	C	D	E	F	Part Number
EMI Shield, 40mm	1.654 (42.0)	1.260 (32.0)	R 0.094 (2.4)	0.098 (2.5)	0.118 (3.0)	0.008 (0.2)	MC-QSB-40-01
EMI Shield, 60mm	2.441 (62.0)	1.969 (50.0)	R 0.106 (2.7)	0.138 (3.5)	0.157 (4.0)		MC-QSB-60-01
EMI Shield, 80mm	3.228 (82.0)	2.815 (71.5)	R 0.126 (3.2)				MC-QSB-80-01
EMI Shield, 92mm	3.700 (94.0)	3.248 (82.5)		0.157 (4.0)	0.177 (4.5)		MC-QSB-92-01
EMI Shield, 4119m	4.764 (121.0)	4.133 (105.0)	R 0.165 (4.2)		0.217 (5.5)	0.012 (0.3)	MC-QSB-119-01

Dimensions: Inches (Millimetres)

Part Number Explanation




Fan Vibration Absorber

For Fans from 40mm to 119mm



Filter Media

Material : Foam dust filter FL100.
 Filter Class : G2 DIN EN 779.
 Material Thickness : ca. 5mm.




Specifications

Description	A	B	C	D	Part Number
Fan Filter, 40mm	1.575 (40.0)	1.260 (32.0)	R 0.118 (3.0)	0.197 (5.0)	MC-QF-40-01
Fan Filter, 60mm	2.362 (60.0)	1.969 (50.0)	R 0.138 (3.5)		MC-QF-60-01
Fan Filter, 80mm	3.150 (80.0)	2.815 (71.5)	R 0.157 (4.0)		MC-QF-80-01
Fan Filter, 92mm	3.622 (92.0)	3.248 (82.5)	R 0.177 (4.5)		MC-QF-92-01
Fan Filter, 119mm	4.685 (119.0)	4.133 (105.0)	R 0.217 (5.5)		MC-QF-119-01

Dimensions: Inches (Millimetres)

Part Number Explanation




Fan Vibration Absorber

For Fans from 40mm to 119mm



Rivets

Material : Plastic.
Color : Black.
Equal Guideline : 2002/95/EG (RoHS compliant).



Specifications

Description	Part Number
Fan Fasteners, Rubber PK10	MC-QF-40-01



Fan Vibration Absorber

For Fans from 40mm to 119mm



Notes:

International Sales Offices:



AUSTRALIA – Farnell

Tel No: ++61 1300 361 005
Fax No: ++61 1300 361 225



FINLAND – Farnell

Tel No: ++358 9 560 7780
Fax No: ++358 9 345 5411



ITALY – Farnell

Tel No: ++39 02 93 995 200
Fax No: ++39 02 93 995 300



SPAIN – Farnell

Tel No: 901 20 20 80
Fax No: 901 20 20 90



AUSTRIA – Farnell

Tel No: ++43 662 2180 680
Fax No: ++43 662 2180 670



FRANCE – Farnell

Tel No: ++33 474 68 99 99
Fax No: ++33 474 68 99 90



MALAYSIA – Farnell-Newark

Tel No: ++60 3 7873 8000
Fax No: ++60 3 7873 7000



SWEDEN – Farnell

Tel No: ++46 8 730 50 00
Fax No: ++46 8 83 52 62



BELGIUM – Farnell

Tel No: ++32 3 475 2810
Fax No: ++32 3 227 3648



GERMANY – Farnell

Tel No: ++49 89 61 39 39 39
Fax No: ++49 89 613 59 01



NETHERLANDS – Farnell

Tel No: ++31 30 241 7373
Fax No: ++31 30 241 7333



SWITZERLAND – Farnell

Tel No: ++44 204 64 64
Fax No: ++44 204 64 54



BRAZIL – Farnell-Newark

Tel No: ++55 11 4066 9400
Fax No: ++55 11 4066 9410



HONG KONG – Farnell-Newark

Tel No: ++852 2268 9888
Fax No: ++852 2268 9899



NEW ZEALAND – Farnell

Tel No: 0800 90 80 80
Fax No: 0800 90 80 81



UK – Farnell

Tel No: ++44 8701 200 200
Fax No: ++44 8701 200 201



CHINA – Farnell-Newark

Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



HUNGARY – Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



NORWAY – Farnell

Tel No: 800 146 70
Fax No: 800 146 76



UK – CPC

++44 8701 202 530
++44 8701 202 531



CZECH REPUBLIC – Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



INDIA – Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



PORTUGAL – Farnell

Tel No: ++34 93 475 8804
Fax No: ++34 93 474 5288



USA – Newark

Tel No: 800 463 9275



DENMARK – Farnell

Tel No: ++45 44 53 66 44
Fax No: ++45 44 53 66 06



IRELAND – Farnell

Tel No: ++353 1 830 9277
Fax No: ++353 1 830 9016



RUSSIA – Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



SINGAPORE – Farnell-Newark

Tel No: ++65 6788 0200
Fax No: ++65 6788 0300



ESTONIA – Farnell

Tel No: ++358 9 560 7780
Fax No: ++358 9 345 5411



ISRAEL – Farnell

Tel No: ++180 937 0015
Fax No: ++180 937 0014



EXPORT – Farnell

Tel No: ++44 8701 200 208
Fax No: ++44 8701 200 209

For enquiries from all other markets

<http://www.farnell.com>
<http://www.newark.com>
<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2007.

