

620ES050 Strain Relief Direct Coupling - Straight

CONNECTOR DESIGNATOR

E


DIRECT COUPLING

620ES050 M 16

Basic Part No. _____

Finish (Table II) _____

Shell Size _____



See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: CABLE ENTRY					
Shell Size	E Max	F Max	G Dia ± .030 (0.8)		
08	.950 (24.1)	.742 (18.8)	.186	(4.7)	
10	.950 (24.1)	.873 (22.2)	.270	(6.9)	
12	.950 (24.1)	.972 (24.7)	.450	(11.4)	
14	1.185 (30.1)	1.078 (27.4)	.460	(11.7)	
16	1.185 (30.1)	1.242 (31.5)	.610	(15.5)	
18	1.185 (30.1)	1.345 (34.2)	.690	(17.5)	
20	1.185 (30.1)	1.472 (37.4)	.816	(20.7)	
22	1.185 (30.1)	1.597 (40.6)	.940	(23.9)	
24	1.185 (30.1)	1.724 (43.8)	1.066	(27.1)	

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.