

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301030016](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Grounded Guard, Cord Type 16/3 SOOW, 15.24m (50.0') Cord Length

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130103
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Overview	Hand Lamps
Product Name	Watertite
Type	Hand Lamps
UPC	78678861302
Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Grounded, Screw Release
Height	457.20mm (18.000")
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	3220.505/g
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC
Material Info	
Engineering Number	1203B163



EU ELV Not Relevant	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130103](#) Series