


SWAGE MOUNT



.120 (3.0)
Plug



CAT. NO. 452


MATERIAL:

Spring: Beryllium Copper
Body: Brass, Silver Plate



.120 (3.0)
Plug

SOLDER CONNECTION



MATERIAL:

Spring: Beryllium Copper, Nickel Plate
Body: Brass, Nickel Plate
Handle: Nylon


CAT. NO.	COLOR
6076	RED
6077	BLACK

BANANA JACKS

INSULATED SOLDER CONNECTION



Accepts
.175 (4.5)
Plug



Supplied with hardware
Unassembled

CAT. NO.	HEAD COLOR
6093	RED
6094	BLACK

MATERIAL:


Body: Brass, Nickel Plate
Terminal: Copper, Tinned
Hex Head: Phenolic

NON-INSULATED RECESSED HEAD

Fits panel up to .312 (7.9) thick



Accepts
.175 (4.5)
Plug



Supplied with nut and lug.
Unassembled

CAT. NO. 6095


MATERIAL:

Current Rating: 15 Amps
Body: Brass, Nickel Plate
Terminal: Brass, Tin Plate

NON-INSULATED MINIATURE JACK



Accepts
.120 (3.0)
Plug



Supplied with lug and nut.
Unassembled

CAT. NO. 6090


MATERIAL:

Body: Brass, Nickel Plate
Terminal: Copper, Tinned

FULLY INSULATED



Accepts
.175 (4.5)
Plug



CAT. NO.	COLOR
6091	RED
6092	BLACK

MATERIAL:


Body: Nylon
Contact: Brass, Tin Plate

NON-INSULATED STANDARD HEAD

Fits panel up to .375 (9.6) thick



Accepts
.175 (4.5)
Plug



Supplied with nut and lug.
Unassembled

CAT. NO. 6096


MATERIAL:

Current Rating: 15 Amps
Body: Brass, Nickel Plate
Terminal: Brass, Tin Plate

NON-INSULATED

MINIATURE

Accepts
.120 (3.0)
Plug




MATERIAL:

Brass, Tin Plate

CAT. NO.	L
476-2	.125 (3.2)
476-3	.165 (4.2)
476-4	.187 (4.7)

STANDARD

Accepts
.175 (4.5)
Plug



MATERIAL:

Brass, Nickel Plate

CAT. NO.	L
575-4	.218 (5.5)
575-6	.265 (6.7)
575-8	.350 (8.9)