


DIN 3110,
ISO 3318,
ISO 1085,
ISO 10102



6 Double open ended spanner

Slim pattern, oval shaft.

GEDORE vanadium steel 31CrV3, mat. No. 1.2208, chrome-plated, smooth finish.

* not standardised

Code	No.	L mm	a	b ₁	b ₂	↔
6063400	6 4x4,5*	100	3,4	13,0	14,0	10
6063590	6 4x5*	100	3,4	13,0	14,0	10
6063670	6 5x5,5*	100	3,4	14,5	16,0	10
6063750	6 5,5x7*	122	3,5	16,0	17,5	20
6063830	6 6x7	122	3,5	16,5	17,5	20
6063910	6 6x8*	122	3,5	16,5	20,5	20
6064050	6 7x8	140	3,8	17,5	20,5	25
6064130	6 7x9*	140	3,8	17,5	22,5	25
6064210	6 8x9	140	3,8	20,0	22,5	25
6064480	6 8x10	140	4,0	20,0	23,5	30
6064560	6 9x10*	157	4,5	22,0	23,5	40
6064640	6 9x11*	157	4,5	22,0	26,0	40
6064720	6 10x11	157	4,5	23,5	26,5	40
6064800	6 10x12*	157	4,5	23,5	28,0	40
6064990	6 10x13	172	5,0	23,5	30,5	55
6065020	6 10x14*	172	5,0	23,5	32,0	55
6065100	6 11x13	172	5,0	26,5	30,5	55
6065290	6 11x14*	172	5,0	26,5	32,0	55
6065370	6 12x13	172	5,0	28,0	30,5	60
6065450	6 12x14	172	5,0	28,0	32,0	60
6065530	6 13x14	178	5,0	30,5	32,0	60
6065610	6 13x15	188	5,5	30,5	34,5	70
6068980	6 13x16	190	5,5	30,5	35,5	100
6065880	6 14x15	188	5,5	32,0	35,5	70
6065960	6 13x17	205	6,0	30,5	38,5	110
6066180	6 14x17	205	6,0	32,0	38,5	110
6066260	6 16x17	205	6,0	35,5	38,5	110
6066340	6 16x18	205	6,0	35,5	40,5	110
6066420	6 17x19	222	6,5	38,5	43,0	155
6066500	6 18x19	222	6,5	40,5	43,0	155
6069360	6 18x21	236	7,0	40,5	46,0	200
6066690	6 17x22*	236	7,0	38,5	48,5	210
6066770	6 19x22	236	7,0	43,0	48,5	210
6066850	6 20x22	236	7,0	44,5	48,5	210
6066930	6 19x24	250	7,5	43,0	53,5	240
6067070	6 21x23	247	7,5	46,0	50,0	240
6069440	6 21x24	250	7,5	46,0	53,5	250
6067150	6 22x24	250	7,5	48,5	53,5	240
6067230	6 22x27*	266	8,0	48,5	60,0	300
6067310	6 24x26	266	8,0	53,5	56,5	300
6067580	6 24x27	266	8,0	53,5	60,0	300
6067660	6 24x30	280	8,5	53,5	63,5	355
6067740	6 25x28	280	8,5	55,0	60,0	355
6067820	6 27x29*	302	9,0	58,0	63,5	460
6067900	6 27x30	302	9,0	60,0	63,5	460
6068040	6 27x32	302	9,0	60,0	68,0	460
6068120	6 30x32	302	9,0	63,5	68,0	460
6069520	6 30x34	302	9,0	63,5	72,0	540
6068200	6 30x36	328	9,4	63,5	76,0	650
6068390	6 32x36	328	9,4	68,0	76,0	650

Code	No.	L mm	a	b ₁	b ₂	↔
6069600	6 34x36	328	9,4	72,0	76,0	560
6068470	6 36x41	360	10,0	76,0	84,5	830
6068550	6 38x42*	360	10,0	77,0	86,0	830
6068630	6 41x46	400	10,7	84,5	93,5	1150
6068710	6 46x50	450	11,6	93,5	102,0	1500
Code	No.	L mm	a	b ₁	b ₂	↔
6070020	6 1/4x5/16AF	122	3,7	17,5	20,0	20
6070100	6 5/16x3/8AF	140	4,0	20,0	23,5	25
6060060	6 5/16x11/32AF	140	4,0	20,5	22,5	40
6070290	6 3/8x7/16AF	157	4,5	23,5	26,5	40
6070370	6 7/16x1/2AF	172	5,0	26,5	30,0	55
6070450	6 1/2x9/16AF	190	5,5	30,0	33,0	70
6070530	6 9/16x5/8AF	190	5,5	33,0	36,0	70
6070610	6 19/32x11/16AF	205	6,0	34,5	39,5	110
6070880	6 5/8x11/16AF	205	6,0	36,0	39,5	110
6070960	6 5/8x3/4AF	222	6,5	36,0	42,5	155
6071180	6 11/16x3/4AF	222	6,5	39,5	42,5	155
6071260	6 3/4x25/32AF	222	6,5	42,5	43,5	155
6071340	6 3/4x7/8AF	236	7,0	42,5	48,5	210
6071420	6 25/32x13/16AF	236	7,0	44,5	46,0	210
6071500	6 13/16x7/8AF	236	7,0	46,0	48,5	210
6071690	6 7/8x15/16AF	250	7,5	48,5	52,0	240
6073550	6 7/8x1.1/16AF	266	8,0	48,5	60,0	310
6071770	6 15/16x1AF	266	8,0	52,0	55,0	300
6071850	6 15/16x1.1/8AF	280	8,5	56,0	63,5	355
6071930	6 1x1.1/8AF	280	8,5	55,0	61,0	355
6072070	6 1.1/16x1.1/8AF	302	9,0	58,0	64,5	460
6072150	6 1.1/16x1.1/4AF	302	9,0	60,0	68,0	460
6072230	6 1.1/8x1.5/16AF	302	9,0	65,5	70,5	460
6072310	6 1.3/16x1.5/16AF	302	9,0	65,5	70,5	460
6072580	6 1.1/4x1.3/8AF	328	9,4	69,5	75,5	650
6072660	6 1.1/4x1.7/16AF	328	9,4	69,5	75,5	650
6072740	6 1.5/16x1.1/2AF	328	9,4	74,0	79,0	650
6072820	6 1.3/8x1.1/2AF	328	9,4	74,0	79,0	650
Code	No.	L mm	a	b ₁	b ₂	↔
6074440	6 1/8x3/16W	157	4,5	21,0	27,0	40
6074520	6 3/16x1/4W	172	5,0	27,0	31,0	55
6074600	6 1/4x5/16W	190	5,5	31,0	35,0	70
6074790	6 5/16x3/8W	205	6,0	35,0	40,5	110
6074870	6 3/8x7/16W	236	7,0	40,5	46,0	210
6074950	6 7/16x1/2W	250	7,5	46,0	51,0	240
6075090	6 1/2x9/16W	266	8,0	51,0	55,5	300
6075250	6 9/16x5/8W	280	8,5	56,0	63,5	355
6075330	6 9/16x11/16W	280	8,5	56,0	63,5	355
6075410	6 5/8x3/4W	302	9,0	65,5	70,5	460
6075680	6 11/16x3/4W	302	9,0	65,5	70,5	460
6075840	6 3/4x7/8W	328	9,4	74,0	79,0	650
6075920	6 7/8x1.W	360	10,0	77,0	86,0	830

DIN 3110, ISO 3318, ISO 1085, ISO 10102



6 Double open ended spanner set

Boxed in illustrated cartons.

H = set in stable plastic holder.



Code	No.	Ø mm / O"AF	↔
6076810	6-6	6x7 8x9 10x11 12x13 14x15 16x17	350
6077380	6-8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	750
6077540	6-10	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27	1300
6077620	6-100	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 24x27 30x32	1250
6077700	6-12	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x26 25x28 27x32	2050
6077890	6-120	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27 25x28 30x32	2150
6078350	6-122 ISO	6x7 8x9 10x11 12x13 14x15 16x18 17x19 20x22 21x23 24x26 27x32 30x34	2600
6079400	H 6-8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	900
6079670	H 6-12	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x26 25x28 27x32	2350
6079750	H 6-120	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27 25x28 30x32	2200
6078000	6-600 A	3/8x7/16 1/2x9/16 5/8x11/16 3/4x25/32 13/16x7/8 15/16x1" AF	850
6078270	6-8 A	1/4x5/16 5/16x3/8 7/16x1/2 9/16x5/8 19/32x11/16 3/4x25/32 13/16x7/8 15/16x1" AF	950
6078510	6-12 A	1/4x5/16 5/16x3/8 3/8x7/16 7/16x1/2 1/2x9/16 9/16x5/8 19/32x11/16 5/8x3/4 3/4x7/8 25/32x13/16 15/16x1 1.1/16x1.1/8" AF	1650