



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Fine Gauge Exposed Welded Tip Thermocouple - Type K or T (IEC)



- ◆ Type K or T fine gauge thermocouple
- ◆ Available as singles or packs of 5
- ◆ 0.003" (0.076mm) conductors
- ◆ Fast response, welded tip exposed junction
- ◆ 0.5, 1 & 2 metres long
- ◆ Teflon® PFA insulated wires
- ◆ IEC colour coded
- ◆ Temperature range -75°C to +260°C
- ◆ Ideal for test & development applications

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

T/C Type	Conductors	Length	+/-	Manufacturing Part No.	Farnell order code
<u>Singles</u>					
'K'	1/0.076mm	0.5 metre	Green /White	XF-853-FAR	242-0342
'K'	1/0.076mm	1 metre	Green /White	XF-854-FAR	242-0343
'K'	1/0.076mm	2 metre	Green /White	XF-855-FAR	242-0344
'T'	1/0.076mm	0.5 metre	Brown/White	XF-856-FAR	242-0345
'T'	1/0.076mm	1 metre	Brown/White	XF-857-FAR	242-0346
'T'	1/0.076mm	2 metre	Brown/White	XF-858-FAR	242-0347
<u>Pack of 5</u>					
'K'	1/0.076mm	1 metre	Green /White	XF-389-FAR	859-8240
'T'	1/0.076mm	1 metre	Brown/White	XF-390-FAR	859-8258

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com