


Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	6 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	7/8 in.
Stud Size	#6
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90 ° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BLUE
Panduit Die Index No. on Barrel	P24
Alternate Industry Die Index No. () on Barrel	(7)



											PANDUIT CORP.	TINLEY PARK, ILLINOIS
											LCAN6-6-L Copper Lug - One-Hole, Narrow Tongue, Standard Barrel	
01		11/08	DRL	DRL						TONGUE THICKNESS WAS .09±.01		
REV		DATE	BY	CHK						DESCRIPTION	SCALE N/A	DRAWING NO / CAD FILE LCAN6-6-CUST

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[LCAN6-6-L](#)