


LOC	DIST	REVISIONS				
AD	00	REV	LTR	DESCRIPTION	DATE	DWN
		—		SEE SHEET 1	—	—

7	2.515	49	100	8-104118-7
	2.015	39	80	8-104118-6
	1.815	35	72	8-104118-5
	1.515	29	60	8-104118-4
	1.115	21	44	8-104118-3
	1.015	19	40	8-104118-2
	.865	16	34	8-104118-1
	.765	14	30	8-104118-0
	.665	12	26	7-104118-9
	.615	11	24	7-104118-8
	.515	9	20	7-104118-7
	.415	7	16	7-104118-6
	.365	6	14	7-104118-5
	.315	5	12	7-104118-4
	.265	4	10	7-104118-3
	.215	3	8	7-104118-2
	1.265	24	50	7-104118-1
4	2.515	49	100	6-104118-7
	2.015	39	80	6-104118-6
	1.815	35	72	6-104118-5
	1.515	29	60	6-104118-4
	1.115	21	44	6-104118-3
	1.015	19	40	6-104118-2
	.865	16	34	6-104118-1
	.765	14	30	6-104118-0
	.665	12	26	5-104118-9
	.615	11	24	5-104118-8
	.515	9	20	5-104118-7
	.415	7	16	5-104118-6
	.365	6	14	5-104118-5
	.315	5	12	5-104118-4
	.265	4	10	5-104118-3
	.215	3	8	5-104118-2
	1.265	24	50	5-104118-1
FINISH	B	A	NO OF POSN	PART NUMBER

6	2.515	49	100	3-104118-7
	2.015	39	80	3-104118-6
	1.815	35	72	3-104118-5
	1.515	29	60	3-104118-4
	1.115	21	44	3-104118-3
	1.015	19	40	3-104118-2
	.865	16	34	3-104118-1
	.765	14	30	3-104118-0
	.665	12	26	2-104118-9
	.615	11	24	2-104118-8
	.515	9	20	2-104118-7
	.415	7	16	2-104118-6
	.365	6	14	2-104118-5
	.315	5	12	2-104118-4
	.265	4	10	2-104118-3
	.215	3	8	2-104118-2
	1.265	24	50	2-104118-1
1	2.515	49	100	1-104118-7
	2.015	39	80	1-104118-6
	1.815	35	72	1-104118-5
	1.515	29	60	1-104118-4
	1.115	21	44	1-104118-3
	1.015	19	40	1-104118-2
	.865	16	34	1-104118-1
	.765	14	30	1-104118-0
	.665	12	26	104118-9
	.615	11	24	104118-8
	.515	9	20	104118-7
	.415	7	16	104118-6
	.365	6	14	104118-5
	.315	5	12	104118-4
	.265	4	10	104118-3
	.215	3	8	104118-2
	1.265	24	50	104118-1
FINISH	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES



MATERIAL: HOUSING: THERMOPLASTIC
COLOR: BLACK
CONTACT: COPPER ALLOY

SEE TABLE

DWN: D. CLOUSER
CHK: T. ZOLA
REV: T. ZOLA

03OCT88
03OCT88
03OCT88

PRODUCT SPEC: 108-1093
APPLICATION SPEC: 114-25031

WEIGHT: —

CUSTOMER DRAWING

NAME: HEADER ASSEMBLY, RIGHT ANGLE, UNSHROUDED, DOUBLE ROW, AMPMODU® System 50

SIZE: A1
CAGE CODE: 00779
DRAWING NO: 104118

RESTRICTED TO: —

SCALE: 5:1
SHEET: 2 OF 2
REV: U

TE Connectivity