




LOC	DIST	REVISIONS					
AJ	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			Y4	REVISED PER ECO-14-016186	27MAR2015	GG	MC

- △ USE PRO—CRIMPER II: 354940—1
2. USE INSTRUCTION SHEET 9766
- △ SPECIAL PACKAGING: BULK PACKAGE 25 PIECES
- △ SPECIAL PACKAGING: BULK PACKAGE 100 PIECES



RECOMMENDED STRIP LENGTH
SCALE 4:1



RECOMMENDED STRIP LENGTH
SCALE 4:1
(FOR 413589-5 AND 1-413589-2 ONLY)

OBsolete	AT&T KS 19224 L2 CABLE AND JIS 1.5C-XV	1.07	[.042]	4.52	[.178]	852922-2	227194-2	222001-4	9-413658-2	413657-6	413653-2	9-413589-6
OBsolete	JIS 3C-2V	1.07	[.042]	5.41	[.213]	852922-1	-	-	9-221132-4	1-413657-0	413653-5	9-413589-5
OBsolete	RG-59 TYPE WITH .031 DIA CENTER CONTACT, BELDEN 9266, 9240 & 9259	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-221132-1	413657-8	413653-1	9-413589-4
OBsolete	RG-179/U, 179A/U, 179B/U, 187/U & 187A/U	1.07	[.042]	4.52	[.178]	852922-2	227194-2	222001-4	9-413658-0	413657-6	413653-2	9-413589-3
OBsolete	AT&T 734A	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-221132-3	413657-8	413653-4	9-413589-2
OBsolete	BELDEN 8218 AND JIS 2.5C-2V	1.07	[.042]	4.52	[.178]	852922-2	-	-	9-221132-6	413657-4	413653-2	9-413589-1
OBsolete	RG-59/U, 59A/U & 59B/U	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-221132-1	413657-2	413653-1	9-413589-0
OBsolete	CUSTOM CABLE: C/C=Ø.021, DIELECTRIC=Ø.122, JACKET=Ø.173	1.07	[.042]	5.41	[.213]	852922-1	-	-	9-221132-0	1-413657-0	413653-5	2-413589-1
OBsolete	MONTROSE 8466-3 AND 8299-3	1.07	[.042]	5.41	[.213]	852922-1	-	-	9-221132-0	1-413657-2	413653-5	1-413589-8
OBsolete	BELDEN 8218 AND JIS 2.5C-2V	1.07	[.042]	4.52	[.178]	852922-2	-	-	9-221132-6	413657-4	413653-2	1-413589-7
OBsolete	BELDEN 8218 AND JIS 2.5C-2V	1.07	[.042]	4.52	[.178]	852922-2	-	-	9-221132-6	413657-4	413653-2	1-413589-6
OBsolete	JIS 2.5C-2W	1.07	[.042]	5.41	[.213]	852922-1	-	-	9-221132-0	413657-4	413653-2	1-413589-5
OBsolete	JIS 3C-2W	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-221132-9	1-413657-0	413653-6	1-413589-4
OBsolete	AT&T KS 19224 L2 CABLE AND JIS 1.5C-XV	1.07	[.042]	4.52	[.178]	852922-2	227194-2	222001-4	9-413658-2	413657-6	413653-2	1-413589-3
OBsolete	BELDEN 8281, 9231 & AT&T 728 AND JIS 5C-2V	1.07	[.042]	8.23	[.324]	852922-3	-	-	9-221132-2	413657-8	413653-3	1-413589-2
OBsolete	JIS 3C-2V	1.07	[.042]	5.41	[.213]	852922-1	-	-	9-221132-4	1-413657-0	413653-5	1-413589-1
OBsolete	AT&T 735A C/C=Ø.016, DIELECTRIC=Ø.077, JACKET=Ø.130	1.07	[.042]	4.52	[.178]	852922-2	-	-	9-413658-2	413657-4	413653-2	1-413589-0
OBsolete	RG-59 TYPE WITH .031 DIA CENTER CONTACT, BELDEN 9266, 9240 & 9259	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-221132-1	413657-8	413653-1	413589-9
BY 5413589-8	RG-179/U, 179A/U, 179B/U, 187/U & 187A/U	1.07	[.042]	4.52	[.178]	852922-2	227194-2	222001-4	9-413658-0	413657-6	413653-2	413589-8
OBsolete	AT&T 734A	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-221132-3	413657-8	413653-4	413589-7
OBsolete	TIMES RG-59/U, DOUBLE BRAID, .270 OD JACKET	1.07	[.042]	8.23	[.324]	852922-3	-	-	9-221132-2	413657-2	413653-1	413589-6
OBsolete	BELDEN 8281, 9231 & AT&T 728 AND JIS 5C-2V	1.07	[.042]	8.23	[.324]	852922-3	-	-	9-221132-2	413657-8	413653-3	413589-5
OBsolete	AT&T KS 19224 L2 CABLE AND JIS 1.5C-XV	1.07	[.042]	4.52	[.178]	852922-2	227194-2	222001-4	9-413658-2	413657-6	413653-2	413589-4
OBsolete	BELDEN 8218 AND JIS 2.5C-2V	1.07	[.042]	4.52	[.178]	852922-2	-	-	9-221132-6	413657-4	413653-2	413589-3
OBsolete	RG-59/U, 59A/U & 59B/U	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-221132-1	413657-2	413653-1	413589-2
OBsolete	BELDEN 88241	1.07	[.042]	6.48	[.255]	852922-1	-	-	9-413658-3	413657-2	413653-1	413589-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE D. LAMAN 4-27-90	 TE Connectivity	
DIMENSIONS: INCHES		CHK R. E. RUTH 4/30/90	NAME	
TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P.LC ± - 1 P.LC ± - 2 P.LC ± - 3 P.LC ± - 4 P.LC ± - ANGLES ± - FINISH		APP'D R. E. RUTH 4/30/90	PLUG, 75 OHM, HEX CRIMP, BNC	
MATERIAL -		PRODUCT SPEC APPLICATION SPEC	SIZE A1	CAGE CODE 00779
		WEIGHT -	DRAWING NO C-413589	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 8:1	SHEET 1 OF 1
			REV Y4	