



HEYClip™ Arrow Clips


PANEL THICKNESS RANGE				MOUNTING HOLE DIAMETER RANGE				PART NO.		DESCRIPTION	PART DIMENSIONS							
Maximum		Minimum		Maximum		Minimum		Natural	Black		A Length		B Clip Dia.		C Head Dia.		D Head Height	
in.	mm.	in.	mm.	in.	mm.	in.	mm.				in.	mm.	in.	mm.	in.	mm.	in.	mm.
.100	2,5	.040	1,0	.190	4,8	.180	4,6	0325	0325B	AC 1996	.45	11,4	.22	5,5	.36	9,1	.06	1,5
				.122	3,1	.118	3,0	0315	0315B	AC 15	.39	9,9	.15	3,8				
				.132	3,4	.130	3,3	0302	0302B	AC 2	.38	9,7	.16	4,1	.28	7,1		
.125	3,2	.062	1,6	.165	4,2	.160	4,1	0318	0318B	AC 18 *	.40	10,2	.19	4,7			.06	1,5
				.192	4,9	.182	4,6	0301	0301B	AC 1	.42	10,5	.23	5,7	.36	9,1		
				.212	5,4	.192	4,9	0328	0328B	AC 28	.45	11,4	.24	6,0	.38	9,5		
				.223	5,7	.213	5,4	0307	0307B	AC 7	.45	11,4	.22	5,6	.37	9,4		
.140	3,6	.125	3,2	.132	3,4	.130	3,3	0313	0313B	AC 13	.32	8,1	.16	4,1	.28	7,1	.06	1,5
.145	3,7	.062	1,6	.161	4,1	.151	3,8	0304	0304B	AC 4	.40	10,2	.18	4,6	.28	7,1	.06	1,5
.160	4,1	.062	1,6	.223	5,7	.213	5,4	0305	0305B	AC 5	.52	13,1	.25	6,3	.37	9,4	.06	1,5
				.165	4,2	.192	4,9	0311	0311B	AC 11	.52	13,2	.21	5,2	.37	9,4	.06	1,5
.187	4,7	.062	1,6	.223	5,7	.213	5,4	0326	0326B	AC 1668	.49	12,5	.25	6,3	.63	15,9	.10	2,5
				.125	3,2	.260	6,6	0309	0309B	AC 9	.58	14,6	.29	7,4	.48	12,3	.07	1,8
.250	6,4	.125	3,2	.260	6,6	.250	6,4	0321	0321B	AC 21	.63	16,0	.28	7,1	.50	12,7	.05	1,3
.300	7,6	.290	7,4	.150	3,8	.145	3,7	0314	0314B	AC 14	.53	13,5	.20	5,0	.27	6,9	.07	1,7
.330	8,4	.310	7,9	.192	4,9	.182	4,6	0306	0306B	AC 6 **	.55	14,0	.23	5,7	.38	9,7	.06	1,5
.340	8,6	.062	1,6	.335	8,5	.320	8,1	0317	0317B	AC 17	.90	22,9	.38	9,5	.68	17,3	.07	1,7
.380	9,7	.360	9,1	.260	6,6	.250	6,4	0316	0316B	AC 16	.81	20,6	.28	7,0	.61	15,5	.07	1,7
.750	19,1	.500	12,7	.260	6,6	.250	6,4	0324	0324B	AC 24	1.14	28,8	.29	7,3	.61	15,5	.07	1,7

Standard color natural. Consult Heyco for black and other colors.

*AC 18 minimum panel thickness is .032" (0,8 mm), head height is .08" (2,0 mm)

**Not hollow body.

- Hollow body design allows the clip to compress through the mounting hole, then expand back to original shape to lock assembled components securely (PN 0306 does not have a hollow body).
- May be disassembled and reused.
- Offer a low cost way to assemble metal, plastic, composite, wood, and other thin gauge materials.
- Snap into mounting holes with fingertip pressure—no tools required.
- Vibration, abrasion, and corrosion resistant.



Arrow Clip

Heyco® Push-In Fasteners

For Combined Panel Thickness up to .375" (9,5 mm)


PANEL THICKNESS		MOUNTING HOLE DIA.		PART NO.		DESCRIPTION	PART DIMENSIONS							
				Natural	Black		A Length		B Clip Dia.		C Head Dia.		D Head Height	
in.	mm.	in.	mm.				in.	mm.	in.	mm.	in.	mm.	in.	mm.
.065	1,7	.165	4,2	0351	0351B	PF 065-165	.20	5,1	.20	5,1	.34	8,7	.12	3,1
.093	2,4	.093	2,4	0340	0340B	PF 093-093*	.17	4,3	.11	2,7	.28	7,1	.03	0,7
.098	2,5	.245	6,2	0384	0384B	PF 098-245	.27	6,8	.28	7,1	.50	12,7	.06	1,4
.125	2,9	.125	3,2	0339	0339B	PF 125-125	.20	5,1	.15	3,7	.25	6,4	.04	1,0
		.089	2,3	0341	0341B	PF 121-089*	.21	5,3	.15	3,7	.31	7,9	.04	1,0
.121	3,1	.115	2,9	0347	0347B	PF 121-115	.25	6,2	.14	3,6	.20	5,2	.04	1,0
		.200	5,1	0358	0358B	PF 121-200	.27	7,0	.24	6,1	.47	11,9	.05	1,3
.133	3,4	.175	4,4	0350	0350B	PF 133-175	.27	6,9	.20	5,1	.34	8,7	.04	1,0
.156	4,0	.115	2,9	0343	0343B	PF 156-115	.29	7,4	.14	3,6	.20	5,2	.04	1,0
		.210	5,3	0360	0360B	PF 156-210	.31	7,8	.23	5,8	.47	11,9	.05	1,3
.171	4,3	.260	6,6	0370	0370B	PF 171-260	.36	9,1	.30	7,5	.59	15,1	.06	1,5
.190	4,8	.155	3,9	0342	0342B	PF 190-155	.28	7,1	.18	4,6	.20	5,2	.04	1,0
.237	6,0	.200	5,1	0352	0352B	PF 237-200	.39	9,8	.24	6,0	.47	11,9	.05	1,3
		.200	5,1	0353	0353B	PF 250-200	.42	10,8	.22	5,7	.34	8,7	.06	1,5
.250	6,4	.218	5,5	0362	0362B	PF 250-218	.36	9,1	.28	7,2	.41	10,3	.05	1,1
		.240	6,1	0371	0371B	PF 250-240	.43	10,9	.30	7,5	.59	15,1	.06	1,5
.375	9,5	.200	5,1	0361	0361B	PFT 375-200	.51	13,0	.24	6,0	.34	8,7	.04	1,0

Standard color natural. Consult Heyco for black and other colors.

*No slot

Material Nylon 6/6
Flammability Rating 94V-2
Temperature Index 257°F (125°C)

- Slotted leg design allows for both compression through the mounting hole and then expansion back to original shape—to lock assembled components securely.
- May be disassembled and reused.
- Offer a low cost way to assemble metal, plastic, composite, wood, and other thin gauge materials.
- Snap into mounting holes with fingertip pressure—no tools required.
- Vibration, abrasion, and corrosion resistant.



Push-In Fastener

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3498](#)