



DESCRIPTION: MALE - 0.370 RIGHT ANGLE - MACHINED - ECONOMY



MEETS IP67 STANDARDS
(SEE PAGE 3 FOR SEALING DETAILS)

MATERIAL:

SHELL: STEEL, NICKEL PLATED
INSULATOR: UL 94V-O RATED, WHITE PA6T
PROCESS TEMP.: 260° C
CONTACT: BRASS
SEALING MATERIAL: F08 FLEXIBLE ADHESIVE

ELECTRICAL:

CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 mOhms Max.
INSULATION RESISTANCE: 1,000 MOhms min.
VOLTAGE: 500VAC FOR 1 MINUTE
TEMPERATURE: -50° C TO 100° C

RoHS COMPLIANT




No. OF PINS	DIMENSIONS							
	A	B	C	D	E	F	G	H
9	1.213	0.984	0.666	0.329	0.236	0.756	0.496	0.427
	30.80	24.99	16.92	8.36	5.99	19.20	12.60	10.85
15	1.541	1.312	0.994	0.329	0.236	1.091	0.496	0.427
	39.15	33.32	25.25	8.36	5.99	27.70	12.60	10.85
25	2.087	1.852	1.534	0.329	0.236	1.618	0.496	0.427
	53.00	47.04	38.96	8.36	5.99	41.10	12.60	10.85

774-EYY-1 1 3 R YY 1

SERIES
POSITIONS
E09
E15
E25
GENDER
1 = MALE
TERMINATION
1 = THROUGH HOLE
SHELL PLATING
3 = NICKEL (GROUND INDENTS)
RoHS COMPLIANT
HARDWARE OPTIONS
00 = NO HARDWARE
01 = .065" CLINCH NUT (BOARD SIDE)
14 = SHORT BRACKET WITH 4-40 SCREW LOCK
PLATING OPTIONS
1 = GOLD FLASH
2 = 30 MICRO-INCH GOLD

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-26-09	
		CHECKED:		DATE:	
	SCALE: 1 : 1		SHEET 1 OF 3		REV 4
	DWG NO. 774-EYY-113RYY1				



* TYP. ON ALL SIZES
UNLESS NOTED OTHERWISE

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 06-10-09	
		CHECKED:		DATE:	
NorComp	SCALE: 1 : 1		SHEET 2 OF 3		REV 4
	DWG NO. 774-EYY-113RYY1				




FRONT SEAL APPLIED OVER INSULATOR
AND BETWEEN FRONT & REAR SHELLS

HARDWARE OPTIONS

14 = SHORT BRACKET & 4-40 SCREW LOCK




MOUNTING BRACKET



SCREW LOCK

01 CLINCH NUT OPTION

01X 0.065" (BOARD SIDE) - CN1



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 06-10-09	
		CHECKED:		DATE:	
NorComp		SCALE: 2.5 : 1	SHEET 3 OF 3		REV 4
		DWG NO. 774-EYY-113RYY1			