






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 19  
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

| REVISIONS |      |     |                           |  | DATE    | APPROVED |
|-----------|------|-----|---------------------------|--|---------|----------|
| REV       | ZONE | LTR | DESCRIPTION               |  |         |          |
| 1         |      | G   | REVISED PER ECR-12-013459 |  | 10DEC12 | PD       |
|           |      |     |                           |  |         |          |
|           |      |     |                           |  |         |          |



NOTE:

- 1. DIMENSIONS IN BRACKETS ARE IN INCHES
- 2. CONTINUOUS STRIP ON REELS

| INSERTION/EXTRACTION REQUIREMENTS | 1ST ON MAX (RES) | 1ST OFF |
|-----------------------------------|------------------|---------|
| TEST TAB - 62061-1                | E                | 3       |

METRIC

|                                                                                                        |  |                                                               |  |                                                |  |                  |  |
|--------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------|--|------------------------------------------------|--|------------------|--|
| [22-16] 0.5 - 1.4 mm <sup>2</sup>                                                                      |  | #                                                             |  | [.020 <sup>±.001</sup> ] <sup>±.001</sup> 0.51 |  | 63233-1          |  |
| WIRE SIZE                                                                                              |  | INSULATION RANGE                                              |  | TAB. THK                                       |  | PART NO          |  |
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES - mm TOLERANCES ON: DECIMALS [±.015] 0.38 ANGLES ± |  | CONTRACT NO DR <i>RR</i> 7-28-82 CHK <i>G. Yetter</i> 7/29/82 |  | TE Connectivity                                |  |                  |  |
| MATERIAL BRASS                                                                                         |  | APPD <i>C. Meyers</i> 7-30-82 APPD <i>V. K...</i> 11-16-82    |  | NAME .110 FLAG FASTON RECEPTACLE               |  |                  |  |
| FINISH PRE-TIN                                                                                         |  | DSGN APPD OTHER APPD                                          |  | SIZE B FSCM NO 00779                           |  | DRAWING NO 63233 |  |
|                                                                                                        |  |                                                               |  | SCALE #                                        |  | SHEET            |  |