

home

test & measurement

download

online catalogue T&M

clamp-type test probes

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

- 2 mm system
- 2 mm safety system
- 4 mm system
- 4 mm safety system

sets

miscellaneous

Search

Search

company

corporate association

location maps

fairs and exhibitions

jobs

home

imprint

contact

terms and conditions

sitemap

Home

sockets

4 mm system

sockets

4 mm system

PKI 10 A

search

Search..

Messetermine

No events

PKI 10 A

datasheet for PKI 10 A


article number: 930103188



View Full-Size Image

SKS

SKS Kontakttechnik GmbH

product description:	order number: 930 103-188
description:	Pole terminal with claw edge and captive insulated head and insulated ring. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness up to 2 mm.
typ:	PKI 10 A gelb/gruen yellow/green
system:	4 mm system
order number:	930 103-188
color versions:	
technical data	
type of contact:	spring unloaded socket
type of termination:	M 4 thread
rated voltage:	DC 60 V
rated current:	35 A
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel-plated
housing material:	PF
environmental conditions:	
temperature range:	-25 °C to +100 °C
flammable class:	
housing:	94 V-0
drawing	

© 2009 www.sks-kontakttechnik.eu

Joomla! is Free Software released under the GNU General Public License.