



Dimensions (In.)

Specifications:

- Impedance tolerance (Ω): $600 \pm 25\%$ @ 100MHz
- DC resistance: 1.00Ω max.
- Rated current: 200mA (max.)
- Operating temperature: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
- Storage temperature: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$

Ferrite Chip Beads provide an effective means of EMI/RFI attenuation for electronic equipment. These items are specially designed for flow, reflow, and wave soldering applications.

Your source for quality electronics. Toll-free full service

(800) 346-6873

<http://www.mouser.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[436-1601](#)