



A
B
C
D
E
F




5 FIGURE OF INSERTION

HORIZONTALLY ○



DF57-*S-1.2C
DF57H-*S-1.2C




DIAGONAL ×




DF57-3234SCF



2 STYLE AND DIMENSION OF BOX



2 STYLE AND DIMENSION OF REEL



DETAIL OF PART No. LABEL

HRS		検査
品名コード	CL666-0016-1	
品名	DF57-3234SCF	
数量	40000	
仕様		
LOT No.		
継ぎ目		

SECTION
Lot No.
SPECIFICATION
QUANTITY
PART No.
CODE No.

INSPECTION

- NOTE 1. 1RL:40000 CONTACTS.
2. STYLE OF REEL AND BOX SHOWS IN FIGURE.
3. A MAXIMUM OF 5 REELS ARE PACKED UP IN ONE BOX.
4. PLEASE BE SURE TO CHECK THE FORM OF CRIMPING USING A CABLE. WHEN YOU ADJUST APPLICATOR.
5. AVOID ANGLED INSERTION OF CRIMP CONTACT(DF57-3234SCF) TO MAINTAIN PERFORMANCE RELIABILITY.

NO. MATERIAL FINISH . REMARKS				1 PHOSPHOR BRONZE SURFACE: TIN PLATING 1 μmMIN			
UNITS mm				NO. MATERIAL FINISH . REMARKS			
SCALE 20: 1				DESCRIPTION OF REVISIONS			
COUNT 1				DESIGNED MI. SAKIMURA			
DIS-H-00000127				CHECKED KI. AKIYAMA			
DATE 15.02.16				DRAWING NO. EDC3-335549-00			
APPROVED : KI. AKIYAMA 10.12.02				PART NO. DF57-3234SCF			
CHECKED : HK. UMEHARA 10.12.02				CODE NO. CL666-0016-1-00			
DESIGNED : TS. KUMAZAWA 10.12.02							
DRAWN : TS. KUMAZAWA 10.12.02							