




- ① CABLE RANGE OF 207387-1 WHEN USED WITH FLEXIBLE BOOT (P/N 207241-1) = 5.08-6.35[.200-.250] DIA.
- ② CABLE RANGE OF 207387-2, & 207387-4 WHEN USED WITH FLEXIBLE BOOT (P/N 207241-1) = 6.35-8.89[.250-.350] DIA.
- ③ OBSOLETE PART NUMBER.

8.26 [.325]	2.54 [.100]	9.78 [.385]	② 207387-4 ③
-	-	9.78 [.385]	② 207387-2
-	-	8.26 [.325]	① 207387-1
D	C	B	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± 0.13 [.005]
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL

THERMOPLASTIC
COLOR: BLACK

FINISH

-

DWN
K.FOLTZ
06/20/94

CHK
R.STONE
06/24/94

APVD
A.FRANTUM
08/09/94

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

TE Connectivity

CABLE GRIP, INTERNAL,
SIZE 17, CPC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-207387

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE
2:1

SHEET
1 of 1

REV
H1