

Product SKU: C2428.41.10

Product Description: Communication & Control Cable, Multi-Conductor, Unshielded, UL 2464, NEC Type CM (UL) c(UL), CSA CMG, No. of Conductors: 15, Gauge Size (AWG): 16, Conductor/Strands: 19/.0117, Jacket: Gray PVC, Temperature Range: -20Â°C to +80Â°C - Gray - 1000 Ft. Reel

Product Category: Electronics - Communication & Control Cable, Multi-Conductor - Unshielded-12,14, & 16 AWG - NEC TYPE CM, UL STYLE 2464 (300 volts) - Gray



Product Construction:

- | | |
|-------------|---|
| Conductor: | <ul style="list-style-type: none">• 16 thru 12 AWG fully-annealed, stranded tinned copper per ASTM B-33 |
| Insulation: | <ul style="list-style-type: none">• Color Code: See chart below• Premium grade color-coded PVC |
| Wrap: | <ul style="list-style-type: none">• Mylar separator under jacket |
| Jacket: | <ul style="list-style-type: none">• PVC, gray• Temperature Range: -20Â°C to +80Â°C |

Product Specification:

- | | |
|------------------------------------|--|
| No. of Conductors: | <ul style="list-style-type: none">• 15 |
| Conductor Size (AWG): | <ul style="list-style-type: none">• 16 |
| Conductor/Strands: | <ul style="list-style-type: none">• 19/.0117 |
| Jacket Color: | <ul style="list-style-type: none">• Gray |
| Nominal Insulation Thickness (in): | <ul style="list-style-type: none">• 0.021 |
| Nominal Insulation Thickness (mm): | <ul style="list-style-type: none">• 0.53 |
| Nominal Jacket Thickness (in): | <ul style="list-style-type: none">• 0.032 |

Nominal Jacket Thickness (mm):	0.81
Nominal Outside Diameter (in):	0.530
Nominal Outside Diameter (mm):	13.46
Nominal C-C Capacitance (pF/ft):	30.5
Standard Packaging:	1000' Non-returnable Wood Reels
Standard Package Quantity:	1
UPC #:	079407701339
Footnote:	Nominal Cap. A: Capacitance between conductors
Put-up:	1000
SCC-14:	50079407701333
Cube:	7488
Weight Per Unit of Measure:	.21
ColorOption:	Gray

Product Information:

Applications:	- Intercoms - Internal telephones - Public address systems - Remote control circuits - Suggested voltage rating: 300 Volts - Suitable for EIA RS-232 applications
---------------	---

Compliances:

- CSA CMG (CSA: 60°C)
- Designed to Meet UL 70,000 BTU Vertical Tray Flame Test
- NEC Article 725 Type CL3 (UL: 75°C)
- NEC Article 800 Type CM (UL: 75°C)
- Passes CSA CMG Flame Test
- UL Style 2464 (UL: 80°C, 300V)
- UL Style 2587 (UL: 90°C, 600V)

Packaging:

- 1000' (305 m) Spools or Reels
- 500' (152 m) Spools or Reels
- Other put-ups available- consult Customer Service

Reference Charts

[Color Code Chart](#)

Technical Specifications

[Unit Conversion Factors](#)

[Cable Design Equations - Balanced Pair](#)

[Insulation and Jacket Properties](#)

[Temperature Conversion Chart](#)

[Decimal and Unit Conversion Factors](#)

[Cable Design Equations - Braid Shield](#)

[AWG Conductor Chart](#)

[Conduit Capacity Chart](#)

[Cable Design Equations - Coaxial Cable](#)

[Engineering Prefixes](#)

[Coax Connector Cross Reference](#)

[Glossary](#)

Designed to Meet
UL Vertical Tray
Flame Test

Underwriters Laboratories Inc.



CMG
Certified
Canadian Standard Association

**CAROL
BRAND**

