

OPTIONAL DRAIN WIRE (SEE NOTE 3)

RELEASE PAPER (MFG. OPTION)

BRAID

FILM FOIL

CONDUCTORS

CABLE: TWISTED PAIRS

.026 [0.66] MIN. THICKNESS PVC JACKET

Ø DIM. "A"

PVC JACKET

RELEASE PAPER (MFG. OPTION)

BRAID

FILM FOIL

CABLE: TWISTED PAIRS

3600X/XX XX DW


NUMBER OF CONDUCTORS
(SEE TABLE 1)

DESCRIBE WIRE DETAIL

PAIR	COND	1st CONDUCTOR		COND	2nd CONDUCTOR		PAIR	COND	1st CONDUCTOR		COND	2nd CONDUCTOR	
		SOLID	BAND		SOLID	BAND			SOLID	BAND		SOLID	BAND
1	1	BLACK	RED	2	RED	BLACK	26	51	BROWN	YELLOW	52	YELLOW	BROWN
2	3	BLACK	WHITE	4	WHITE	BLACK	27	53	BROWN	ORANGE	54	ORANGE	BROWN
3	5	BLACK	GREEN	6	GREEN	BLACK	28	55	ORANGE	YELLOW	56	YELLOW	ORANGE
4	7	BLACK	BLUE	8	BLUE	BLACK	29	57	VIOLET	ORANGE	58	ORANGE	VIOLET
5	9	BLACK	YELLOW	10	YELLOW	BLACK	30	59	VIOLET	RED	60	RED	VIOLET
6	11	BLACK	BROWN	12	BROWN	BLACK	31	61	VIOLET	WHITE	62	WHITE	VIOLET
7	13	BLACK	ORANGE	14	ORANGE	BLACK	32	63	VIOLET	GREEN	64	GREEN	VIOLET
8	15	RED	WHITE	16	WHITE	RED	33	65	VIOLET	BLUE	66	BLUE	VIOLET
9	17	RED	GREEN	18	GREEN	RED	34	67	VIOLET	YELLOW	68	YELLOW	VIOLET
10	19	RED	BLUE	20	BLUE	RED	35	69	VIOLET	BROWN	70	BROWN	VIOLET
11	21	RED	YELLOW	22	YELLOW	RED	36	71	VIOLET	BLACK	72	BLACK	VIOLET
12	23	RED	BROWN	24	BROWN	RED	37	73	GRAY	WHITE	74	WHITE	GRAY
13	25	RED	ORANGE	26	ORANGE	RED	38	75	GRAY	BROWN	76	BROWN	GRAY
14	27	GREEN	WHITE	28	WHITE	GREEN	39	77	GRAY	RED	78	RED	GRAY
15	29	GREEN	BLUE	30	BLUE	GREEN	40	79	GRAY	ORANGE	80	ORANGE	GRAY
16	31	GREEN	YELLOW	32	YELLOW	GREEN	41	81	GRAY	YELLOW	82	YELLOW	GRAY
17	33	GREEN	BROWN	34	BROWN	GREEN	42	83	GRAY	GREEN	84	GREEN	GRAY
18	35	GREEN	ORANGE	36	ORANGE	GREEN	43	85	GRAY	BLUE	86	BLUE	GRAY
19	37	WHITE	BLUE	38	BLUE	WHITE	44	87	TAN	ORANGE	88	ORANGE	TAN
20	39	WHITE	YELLOW	40	YELLOW	WHITE	45	89	TAN	GREEN	90	GREEN	TAN
21	41	WHITE	BROWN	42	BROWN	WHITE	46	91	TAN	BLACK	92	BLACK	TAN
22	43	WHITE	ORANGE	44	ORANGE	WHITE	47	93	TAN	BLUE	94	BLUE	TAN
23	45	BLUE	YELLOW	46	YELLOW	BLUE	48	95	TAN	WHITE	96	WHITE	TAN
24	47	BLUE	BROWN	48	BROWN	BLUE	49	97	TAN	YELLOW	98	YELLOW	TAN
25	49	BLUE	ORANGE	50	ORANGE	BLUE	50	99	TAN	BROWN	100	BROWN	TAN

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

NOTES	
1.	REGULATORY INFORMATION: VISIT 3M.com/regs
2.	IN THE EVENT OF CONFLICT BETWEEN THIS DATA AND THAT CONTAINED IN THE PRODUCT SPECIFICATION, THE PRODUCT SPECIFICATION TAKES PRECEDENT.
3.	OPTIONAL DRAIN WIRE, SPECIAL ORDER: 28 AWG, 7 X 36 AWG (7 X Ø0.127) TPC.



SHIELDING: 0.001 [0.03] THICK ALUMINUM/POLYESTER FILM FOIL
AND 90% COVERAGE TINNED COPPER BRAID

NOTE: UNBALANCED IS MEASURED BETWEEN CONDUCTORS WITHIN A PAIR WITH ONE CONDUCTOR CONNECTED TO THE SHIELD.
BALANCED IS MEASURED BETWEEN CONDUCTORS WITHIN A PAIR WITH THE SHIELD FLOATING.

FLAMMABILITY RATING: USA: N.E.C. 725, CL2
CANADA: FT1

UL® CL2 75°C 28 AWG 3M NU **UL**® AWM II A/B 80°C 150V FT1 EU <50V

TABLE 1		
NUMBER OF CONDUCTORS	3M PART NUMBER	DIM. "A" ±.02
14 (7) PAIR	3600X/14	.22 [5.6]
20 (10) PAIR	3600X/20	.24 [6.1]
24 (12) PAIR	3600X/24	.25 [6.4]
26 (13) PAIR	3600X/26	.25 [6.4]
36 (18) PAIR	3600X/36	.29 [7.4]
40 (20) PAIR	3600X/40	.30 [7.6]
50 (25) PAIR	3600X/50	.32 [8.1]
68 (34) PAIR	3600X/68	.36 [9.1]
80 (40) PAIR	3600X/80	.39 [9.9]
100 (50) PAIR	3600X/100	.44 [11.2]

UL[®]
CS

UL FILE NO: E118773,
POWER LIMITED CIRCUIT
CABLE: CL2

DIMENSIONS: INCHES [MM]
[MM] IS FOR REF. ONLY

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
ACCESS CODES				DRFT	CASTIGLIONE		DATE	MFO	DATE
				CHKD			DATE	APPRV. F. RODRIGUEZ	DATE MAY 07, 2024
DIVISION		DIVISION CODE		© 3M COPYRIGHT 2025 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.					
		DEPP							
DO NOT SCALE DRAWING		SCALE		TOLERANCES EXCEPT AS NOTED		3M 3M Center St. Paul, MN 55144			
		INCHES							
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018		MILLIMETERS		TITLE SHIELDED/JACKETED, ROUND, DISC. WIRE CABLE, 28AWG			
MAX SURFACE ROUGHNESS ☒ ALL SURFACES ☐ MARKED ONLY		ANGLES ±							
				CAGE NUMBER		SIZE	DRAWING NO.		REV.
				D		D	578-5100-0388-8		D
				MODEL		3600X		DET. SHTS ☒ YES ☐ NO	
								SHT 1 OF 2	

8

7

6

5

4

3

2

1

3M™ ROUND, SHIELDED/JACKETED, DISCRETE WIRE CABLE, 3600X SERIES

28 AWG STRANDED, TWISTED PAIR, PVC/PVC

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.

3M Company
Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
http://www.3M.com/interconnect

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

DESIGN REFERENCE

NEXT ASSEMBLY

DO NOT SCALE DRAWING

SCALE

TOLERANCES EXCEPT AS NOTED

THIRD ANGLE PROJECTION

INTERPRET PER ASME Y14.5 - 2018

MAX. SURFACE ROUGHNESS

ALL SURFACES

MARKED ONLY

INCHES

MILLIMETERS

ANGLES

REV

ECO

ISSUE DATE AND DESCRIPTION

DRFT

CHKD

DRFT

CASTIGLIONE

DATE

MAY 07, 2024

DATE

MAY 07, 2024

APPR

F. RODRIGUEZ

DATE

MAY 07, 2024

3M

3M Center
St. Paul,
MN 55144

© 3M COPYRIGHT 2025
This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.

TITLE

SHIELDED/JACKETED,
ROUND, DISC. WIRE
CABLE, 28AWG

CAGE NUMBER

SIZE

DRAWING NO.

REV.

MODEL

3600X

DET

LISTs

YES

NO

SHT 2 OF 2

D

C

B

A

D

C

B

A

78-5100-0388-B

Revision