

规格 Specifications

额定负载 Ratings	DC 30 V 0.1 A
初期接触电阻 Initial Contact Resistance	70 mΩ Max.
绝缘电阻 Insulation Resistance	DC 500 V 60 Sec 100 MΩ Min.
抗电强度 Dielectric	AC 500 V (50~60Hz) 60 Sec.

操作力 Operating Force(gf)		(R)
	200±100 gf	300±150 gf
① 负荷寿命 Operating Life With Load	10000 次	Cycles




示意图 SCHEMATIC

安装孔 PIERCING PLAN

①

7	端子 TERMINAL	C2680R	6	Ag PLATED			
6	弹簧 SPRING	SUS	1	NATURAL			
5	胶壳 HOUSING	PBT	1	BLACK C			
4	接触片 CONTACT	C5210R	2	Ag CLAD			
3	锁钩 LOCK HOOK	SUS	1	NATURAL	A01	修改零件列表见①	曹文斌 06-04-18
2	胶柄 KNOB	POM	1	BLACK C		机械寿命变为负荷寿命见①	
1	胶盖 COVER	POM	1	GREY	02		何锦洪 10 JUL 04
序号 NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS	标号 REV	内容 DESCRIPTION	签名 SIGN. 日期 DATE

DWG NO. ITEM0309

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	PUSH SWITCH		ITEM NO	PS-2206-L NS		
UNDER 1	± 0.10		DRAWN	曹文斌		VERSION	A01	PAGE 1 OF 1
1 - 10	± 0.30	REVIEWED	张念明	06-04-18	SCALE		UNIT mm	
OVER 10	± 0.50	APPROVED	林高全	06-04-19	PROJECTION			

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Components:](#)

[PS-2206-L NS](#)