



G3G125 Series

Specialty



Ø 125

■ AC canister blower.

■ Contact application engineering for approvals.

■ Ratings based on a back pressure of 40.15 inches of water (10000 pascal)

Part Number	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Speed (RPM)	Wgt. (lbs)
G3G125-AA20-10	41.2	208-250	50/60	600	71	50	13000	8.16



ebm-papst

e-mail: sales@us.ebmpapst.com · TEL: 860-674-1515 · FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2006 © ebm-papst Inc. reserves the right to change any specifications or data without notice

