


"F" Right Angle Jack

161-R243-EX

KOBI CONN

"F" Right Angle Jack



Dimensions: mm.

MECHANICAL SPECIFICATIONS

Housing:	Brass, nickel plated with copper undercoat
Contact:	Phosphor bronze, tin plated with copper undercoat
Insulator:	Polypropylene
Bracket:	Steel, tin plated with copper undercoat
RoHS Compliant	

ELECTRICAL SPECIFICATIONS

Initial Insertion Force:	13 oz.
Contact Retention:	1 oz. Min.
Contact Resistance:	0.02Ω
Dielectric Strength:	1080V for 1 min.
Insulation Resistance:	10,000 MΩ min. @250V
RoHS Compliant	

Date Last Revised: 8/9/10

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301243

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-R243-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-R243-EX](#)