ED550/XDS



2-16 poles, Spacing 3.5 mm
insert required no. of poles **x**
How to order see page 5

Ratings:		
Rated Voltage	**125 V**	**130 V**
Rated Current	**6 A**	**13.5 A (T60)**
Wire Size	**AWG 28-16**	**1.0 mm²**
Test Voltage		**2.0 kV**
Rated Torque/ScrewSize		**0.4 Nm/M2**
Max. Rated Cross Section		
Single Wire (solid)		**1.5 mm²**
Stranded Wire (flexible)		**1.0 mm²**
Stranded wire with Ferrules		**0.75 mm²**
Dimensions		
Spacing		**3.5 mm**
PCB Hole Diameter		**1.2 mm**
Stripped Length		**5.5 mm**
Materials		
Insulating Material		**PA**
Flammability Class		**UL94 V-0**
Temperature Range		**-30˚C/+105˚C**
Terminal Block		**CuZn**
Wire Guard		**Stainless Steel**
Color		
Grey