

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0039012240
Status: Active
Overview: Mini-Fit Jr.™
Description: 4.20mm (.165") Pitch Mini-Fit Jr.™ Receptacle Housing, Dual Row, UL 94V-2, 24 Circuits

Documents:

- 3D Model
Drawing (PDF)
Test Summary (PDF)
- Product Specification PS-5556-001 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	5557
Comments	Glow Wire Equivalent Part Number 50361667
Overview	Mini-Fit Jr.™
Product Name	Mini-Fit Jr.™

Physical

Breakaway	No
Circuits (maximum)	24
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface (in)	0.165 In
Pitch - Mating Interface (mm)	4.20 mm
Pitch - Term. Interface (in)	0.165 In
Pitch - Term. Interface (mm)	4.20 mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical


CSA	LR19980
TUV	R72081037
UL	E29179

Material Info

Old Part Number	5557-24R
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-5556-001
Sales Drawing	SD-5557-003



Series image - Reference only

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

5557 Series

Mates With

5559d , 5566vw , 5566vwo , 5569rdf ,
5569rdp , 43810a , 43810b , 43810c ,
43810d , 44068a , 44068b , 44068c ,
44068d , 44281 , 44472dw , 44472dwo ,
87427 , 87427r , 87427rf , 42404 , 44474 ,
42440 , 43879 , 42475

Use With

5556 , 44476 , 44485 , 41995

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION