


Terminal Blocks

158-P02142RPU-E, 158-P03142RPU-E, 158-P04142RPU-E, 158-P05142RPU-E,
158-P06142RPU-E, 158-P07142RPU-E, 158-P08142RPU-E, 158-P09142RPU-E,
158-P10142RPU-E, 158-P11142RPU-E, 158-P12142RPU-E

KOBI **CONN**

Terminal Blocks

158-P02142RPU-E, 158-P03142RPU-E, 158-P04142RPU-E, 158-P05142RPU-E, 158-P06142RPU-E, 158-P07142RPU-E,
158-P08142RPU-E, 158-P09142RPU-E, 158-P10142RPU-E, 158-P11142RPU-E, 158-P12142RPU-E



Dimensions: mm (In.)

ELECTRICAL SPECIFICATIONS

Rating:	300V 10A
Pitch:	5.08 mm
Insulation withstands voltage:	AC 1500V/Min
Insulation resistance:	500MΩ or more at DC500V
Temperature range:	-40°C~ +105°C
Electric wire:	22~14 AWG

MATERIAL SPECIFICATIONS

End Cover (5):	PA66, Green
Lever (4):	PA66, Orange
Clamping (3):	Stainless Steel
Solder Pin (2):	Copper, Tin Plated
Housing (1):	PA66, Green
RoHS Compliant	

Date Last Revised: 7-17-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 301019

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[158-P04142RPU-E](#) [158-P08142RPU-E](#) [158-P06142RPU-E](#) [158-P11142RPU-E](#) [158-P12142RPU-E](#) [158-P10142RPU-E](#) [158-P02142RPU-E](#) [158-P09142RPU-E](#) [158-P05142RPU-E](#) [158-P07142RPU-E](#) [158-P03142RPU-E](#)