




## PRODUCT SPECIFICATION

|                        |                                                                    |
|------------------------|--------------------------------------------------------------------|
| <b>CATALOG NUMBER:</b> | See table below                                                    |
| <b>DESCRIPTION:</b>    | Outdoor use SJTW cord set                                          |
| <b>APPROVALS:</b>      | UL Listed and CSA Certified, or UL/CUL Listed Outdoor Use Cord Set |

### CONSTRUCTION PARAMETERS:

|                           |                                             |
|---------------------------|---------------------------------------------|
| Cable type:               | SJTW                                        |
| Conductor:                | See table below                             |
| Jacket material:          | PVC                                         |
| Overall cable O.D. (nom): | See table below                             |
| Cord rating:              | Hard Usage per the National Electrical Code |
| Cable legend:             | Indent print                                |
| Cable color:              | See table below                             |



*Note: Plug and connector style may vary*

|                                |                     |
|--------------------------------|---------------------|
| Attachment plug configuration: | NEMA 5-15P          |
| Cord connector configuration:  | NEMA 5-15R          |
| Plug and connector material:   | PVC                 |
| Plug and connector color:      | Same as cable color |

### ELECTRICAL PROPERTIES:

|                            |                 |
|----------------------------|-----------------|
| Cable temperature rating:  | -40 to +60 °C   |
| Nominal operating voltage: | 125 VAC         |
| Maximum operating current: | See table below |

| Catalog no. | Length | Color  | Conductor     | Cable O.D. (nom) | Current rating |
|-------------|--------|--------|---------------|------------------|----------------|
| 02304       | 10 ft  | Orange | 16/3 26/30 BC | 0.315 in         | 13A            |
| 02305       | 15 ft  | Orange |               |                  |                |
| 02306       | 15 ft  | Black  |               |                  |                |
| 02307       | 25 ft  | Orange |               |                  |                |
| 02308       | 50 ft  | Orange |               |                  |                |
| 02309       | 100 ft | Orange |               |                  | 10 A           |
| 02407       | 25 ft  | Red    | 14/3 41/30 BC | 0.352 in         | 15A            |
| 02408       | 50 ft  | Red    |               |                  | 13A            |
| 02409       | 100 ft | Red    |               |                  |                |

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.