


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS				DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION	
✓	✓		J	REDRAWN-REVISED PER G-1479,	4/14/85 Jmm
✓	✓		K	G-1175, P85-0131 & P85-0132	
✓	✓		L	OBSOLETE 2-242-3/6-2393	3/24/87 BS Jmm
✓	✓		M	REV PER G-4732	7/22/88 Jmm
✓	✓			REV/0720-0066-93	4-12-93 TD/me



1 WIRE INSULATION DIA. = .050-.082

2 BODY FINISH = TIN PLATE (MIL-T-10727).000100

OBSOLETE

QUANTITY	DESCRIPTION	PART NO
50	LOOSE PC. BOX	8-324597-2
100	ON TAPE, 5000	2-324597-3
1000	ON TAPE, LG. BOX	2-324597-2
5000	ON TAPE, REEL	2-324597-1
—	LOOSE PIECE	324597

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.003 ANGLES ±.003		CONTRACT NO		NAME	
MATERIAL INSULATION: NYLON-YELLOW BODY & SLEEVE: COPPER (GG-C576)		DR UTA/RFB 10-2-87		AMP AMP INCORPORATED Harrisburg, Pa.	
FINISH BODY - 2		CHS 11/14/85		TERMINAL P.I.D.G., FLANGED SPADE WIRE SIZE: 26-22	
OTHER APPD		APPD 11/14/85		SIZE B	
		DSGN APPD		FSCM NO 00779	
				DRAWING NO 324597	
				SCALE NTS	
				SHEET 1 OF 1	

CUSTOMER DRAWING