

# Slotted Bits

The ideal multi-purpose bits for all around quality and performance

Made in Germany - Production Quality

Suitable for all applications  
Hardness HRC 59-61  
Suitable for both manual & machine applications



Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened

High resistant to wear and tear for a long tool life



SHOP

**710 Slotted Insert Bit Packs, 1" CVM S2**  
modified tool steel.

Item	⬇	⬇	⬇	⬇	⬇	⬇
No.	mm	mm	Inch	mm	lbs.	2 Bit Pack
710 51	0.6	4.5	.177	25	.03	
710 52	0.8	5.5	.216	25	.03	
710 53	1.2	6.5	.255	25	.03	
710 54	1.6	8.0	.315	25	.03	



SHOP

**710 55 Slotted Insert Bit Packs, 1" CVM S2**  
modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

**710 55 Set includes the following bits:**

⬇	⬇	⬇	⬇	⬇	⬇	⬇
Slotted Sizes:						
wt.	.04	5.5, 6.5, 8.0	x 1"	(25mm)		



SHOP

**740 50 Slotted Power Bit Packs, 2" CVM S2**  
modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

**740 50 Set includes the following bits:**

⬇	⬇	⬇	⬇	⬇	⬇	⬇
Slotted Sizes:						
wt.	.08	4.5, 5.5, 6.5	x 2"	(50mm)		



SHOP

**740 Slotted Power Bit Packs, 2"**

CVM S2 modified tool steel.

Item	⬇	⬇	⬇	⬇	⬇	⬇
No.	mm	mm	lbs.	2 Bit Pack		
740 61	3.0	50	.05			
740 62	3.5	50	.05			
740 63	4.0	50	.05			
740 64	4.0	50	.05			
740 65	4.5	50	.05			
740 66	5.5	50	.05			
740 67	6.5	50	.06			
740 68	8.0	50	.08			
740 69	8.0	50	.08			

## Wiha Slotted Insert Bits and Power Bits



SHOP

**710 Slotted Insert Bits, 1/4" Hex Drive,**  
Length 25mm/.984"

Item	⬇	⬇	⬇	⬇	⬇	⬇
No.	mm	Inch	mm	Inch	pkg.	
710 01	4.5	.177	0.6	.024	10	
710 04	5.5	.216	0.8	.030	10	
710 02	6.5	.255	1.2	.039	10	
710 03	8.0	.315	1.6	.063	10	



SHOP

**743 Slotted and Phillips Double End Bits.**  
1/4" Hex Drive, Length 2.36"/60mm

Item	⬇	⬇	⬇	⬇	⬇	⬇
No.	mm	Size	mm	pkg.	lbs.	
743 03	4.5	x 1	60	10	.22	
743 06	5.5	x 2	60	10	.30	
743 09	7.0	x 3	60	10	.30	



SHOP

**740 Slotted Power Bits, 1/4" Hex Drive,**  
Length 2.0"/50mm 10pk. weight .20 lbs.

Item	⬇	⬇	⬇	⬇	⬇	⬇
No.	mm	Inch	mm	Inch	pkg.	
740 03	3.0	.118	0.5	.020	10	
740 06	3.5	.139	0.6	.024	10	
740 09	4.0	.157	0.5	.020	10	
740 10	4.0	.157	0.8	.030	10	
740 12	4.5	.177	0.6	.024	10	
740 15	5.5	.216	0.8	.032	10	
740 18	6.5	.255	1.2	.039	10	
740 21	8.0	.315	1.2	.039	10	
740 23	8.0	.315	1.6	.063	10	



SHOP

**720 Slotted Insert Bits, 5/16" Hex Drive,**  
Length 41mm

Item	⬇	⬇	⬇	⬇	⬇	⬇
No.	mm	Inch	mm	pkg.	lbs.	
720 48	6.5	.255	1.2	10	.27	
720 49	8.0	.315	1.6	10	.31	
720 50	10.0	.393	1.6	10	.46	
720 51	12.0	.472	2.0	10	.56	

2 bit pack

SHOP

**720 Slotted Insert Bit Packs, 1"**  
CVM S2 modified tool steel. 5/16" Hex Drive.

Item	⬇	⬇	⬇	⬇	⬇	⬇
No.	mm	mm	Inch	mm	lbs.	2 Bit Pack
720 25	1.2	6.5	.255	41	.06	
720 31	1.6	8.0	.315	41	.08	
720 39	1.6	10.0	.393	41	.10	
720 47	2.0	12.0	.472	41	.12	